

Project \_\_\_\_\_

Location \_\_\_\_\_

Type \_\_\_\_\_

# Product Specifications

## 10043

Manufactured by Kichler® Lighting



## DESCRIPTION

### Task Work Direct Wire Fluorescent -

Compact undercabinet lighting that employs energy efficient fluorescent lamping.

## SPECIFICATIONS

### MATERIALS:

Housing: Steel

Lens: PVC

FINISHES: Powder Coated White

### DIMENSIONS:

Length: 34.50"

Width: 3.5"

Height: 1.00"

### LIGHT SOURCE:

- 1 – 21W T5 Fluorescent
- 2700K Color Temperature
- 85 Color Rendering Index (CRI)
- 7500 hour expected life span

### ELECTRICAL DATA:

Input Voltage: 120V AC

Power Consumed: 21 watts

Efficacy: 88.0 lumens/watt

## FEATURES

- C-UL Listed for Cabinet Use – UL Standard No. 2108
- Compact Size
- T5 Fluorescent Lamp (Included)
- On/Off Switch
- Keyhole Mounting
- Built-in Transformer
- Snap-in Etched, Ribbed Diffuser
- Hinged Assembly
- Multiple KO's for Installation Ease
- Side KO's for Optional End-to-End Assembly
- Intended for Connection to Power Through NM/BX Cable Connector (Included)
- Cord and Plug Accessory Available

## PHOTOMETRIC DATA

Countertop Foot-Candle Measurements Available Upon Request.

### FOOT-CANDLE MEASUREMENT ON WORK SURFACE

A	LIGHT OUTPUT FC (COUNTER FRONT)	33.1
B	LIGHT OUTPUT FC (COUNTER MIDDLE)	60.6
C	LIGHT OUTPUT FC (COUNTER BACK)	85.6
D	LIGHT OUTPUT FC (COUNTER WALL)	29.2

