



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	19.00"	2.62"
<u>BP Height</u>	<u>BP Width</u>	
5.25"	5.25"	
<u>Hanging Weight</u>		
4.43 lb		

Lamping:

Incandescent MB Incandescent	3,450 Rated Lumens
3.00 100W MB Incandescent	Color Temperature
300 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
8.09 lb	9.50"	10.00"	22.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209212213	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Wilshire WS

Material:

Steel

Certification:

Damp Location  
Location

Additional:

MB Incandescent (Not Included)  
Lighting Direction: Both