



S9114

9.6A19/LED/2700K/120V/ND
9.6 watt; A19 LED; Frosted; 2700k Medium base; 240° beam spread; 120 volts; Non-Dimmable

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable

This item has been discontinued.
Possible replacement:

- [S9593](#)



S9114

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9114	045923091148	120	9.6	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9.6A19/LED/2700K/120V/ND	Non-Dimmable	Frosted	4-5/8"	2.38"	806	25000	2700

Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL or ETL Listed
Warm White	80	240	Operating temperature: -20°C (-4°F) to a maximum of +45°C (113°F)	24	Box	Yes	Yes

Warranty	Status	Suggested Substitute
3 Year Limited	Discontinued	S9593



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051