



GE
Lighting

89633 - GE G25

FLE15/2/G25XL

Product Photo



GENERAL CHARACTERISTICS

Base Type	Screw-In
Bulb Finishes and Colors	Soft white
Mercury Content	3.5 mg
Rated Life Hours-nominal	10000 h
Starting Temp (MIN) C-degrees	5 °C
Base Description	Medium Screw
Mercury-Picogram per mean lm hr	530.3
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	G25

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	660 lm
Nominal Initial Lumen per Watt	55
Initial Lumens-nominal	825 lm
Color Rendering Index-CRI	82
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	89633
Description	FLE15/2/G25XL
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168896337
Standard Package GTIN	00043168896337
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168896337
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168896337
Standard Package GTIN	10043168896334
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168896337

DIMENSIONS

Nominal Length	4.59 in
Bulb Max Overall Length-MOL	4.59 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Rated power (Watts)	15 W