



Measurements:

<u>Height</u>	<u>Width</u>
8.00"	21.50"
<u>BP Height</u>	<u>BP Width</u>
6.00"	4.25"
<u>Hanging Weight</u>	
4.00 lb	

Lamping:

Incandescent MB Incandescent	0 Rated Lumens
3.00 60W MB Incandescent	Color Temperature
180 total watt	
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
5.57 lb	9.00"	6.00"	23.75"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108455	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: BOTH