

12.5W 120V 60 DEG 3000K Alumin
16206AZT30 (Textured Architectural Bronze)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	4.75"
Length	4.75"
Width	3.00"

Ordering Information

Product ID	16206AZT30
Finish	Textured Architectural Bronze
Available Finishes	BBR, BBR, WHT, WHT, AZT, AZT

Dimensions

Weight	1.15 LBS
--------	----------

Photometrics

Kelvin Temperature	3000K
Color Rendering Index	80

Specifications

Material	Aluminum
Glass Description	60 Beam Spread Optic

Electrical

Voltage	120VAC
Operating Voltage Range	108-130 VAC

Qualifications

Safety Rated	Not Required
Expected Life Span	40000 Hours
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	LED
Lamp Included	Integrated
Number of Lights/LEDs	5
Max or Nominal Watt	12.5W