



## WIDE SLIDE 0-10V PRESET DIMMER WITH INTEGRATED POWER PACK, TRI-COLOR

WS4FBL3PTC | [Pass & Seymour](#)

### FEATURES & BENEFITS

For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.



- For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts.
- Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control.
- Low voltage pig tails labeled separately.
- Preset, Single Pole and 3-Way Operation.
- Green LED glows when OFF to make dimmer easy to find in the dark.
- Sleek, ergonomic P&S Decorator style matches other Decorator devices.
- Wider slide control for easier dimming operation.
- Built-in power pack included.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents?_id=).

### SPECIFICATIONS

#### GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)  
Product Series: Wide Slide  
Type: LED  
Number Of Poles: Single pole, 3-way  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 184  
CSA Standard: Yes  
cULus: Yes

UL Standard: Yes

## **DIMENSIONS**

Depth (US): 1.25"

Height (US): 4.25"

Width (US): 1.75"

## **TECHNICAL INFORMATION**

Amps: 120V 10A/277V 5A

NEMA Rating: Yes

Rating (A): 0-10V

Rating (VAC): 0-10V

Volts (AC): 120VAC/277VAC, 60Hz

Volts (DC): 0-10V

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No