

# ANCHORING DEVICES



## LAG SCREW SHIELD

ALLOY ZINC DIE CAST  
Medium-Duty Application  
See page 78 and 79 for Lag Bolts

A secure die cast expansion anchor of zinc rustproof alloy. Most effective for holding in brittle or soft masonry. The ideal product for mortar joints.

| STOCK NO.    | UPC NO. | LAG SCREW DIAMETER | HOLE SIZE | ANCHOR LENGTH | WT. PER PKG. | STD. PKG. | SUGGESTED TRADE LIST PRICE PER |
|--------------|---------|--------------------|-----------|---------------|--------------|-----------|--------------------------------|
| <b>SHORT</b> |         |                    |           |               |              |           |                                |
| J1201        | 80854   | 1/4                | 1/2       | 1             | 1.06         | 50        | 46.66/c                        |
| J1202        | 80855   | 5/16               | 1/2       | 1 1/4         | 1.21         | 50        | 42.70/c                        |
| J1203        | 80856   | 3/8                | 5/8       | 1 3/4         | 2.19         | 50        | 68.80/c                        |
| J1204        | 80857   | 1/2                | 3/4       | 2             | 1.73         | 25        | 111.40/c                       |
| J1205        | 80858   | 5/8                | 7/8       | 2             | 2.74         | 25        | 171.00/c                       |
| J1206        | 83081   | 3/4                | 1         | 2             | .81          | 25        | 198.05/c <b>NEW</b>            |
| <b>LONG</b>  |         |                    |           |               |              |           |                                |
| J1207        | 80859   | 1/4                | 1/2       | 1 1/2         | 1.48         | 50        | 49.30/c                        |
| J1208        | 80860   | 5/16               | 1/2       | 1 3/4         | 1.45         | 50        | 50.26/c                        |
| J1209        | 80861   | 3/8                | 5/8       | 2             | 3.32         | 50        | 92.86/c                        |
| J1210        | 80862   | 1/2                | 3/4       | 3             | 2.57         | 25        | 141.80/c                       |
| J1211        | 80863   | 5/8                | 7/8       | 3 1/2         | 5.37         | 25        | 271.00/c                       |
| J1212        | 83086   | 3/4                | 1         | 3 1/2         | 1.06         | 25        | 365.26/c <b>NEW</b>            |



## DROP-IN ANCHOR

STEEL ZINC CHROMATE AND STAINLESS STEEL  
FOR USE IN STRUCTURAL FASTENING TO CONCRETE FLOORS  
ONE SETTING TOOL FURNISHED IN EACH JAR OF ANCHORS

| STOCK NO.                      | UPC NO. | SIZE   | HOLE SIZE | ANCHOR LENGTH | STD. PKG. | WT. PER PKG. | SUGGESTED TRADE LIST PRICE PER     |     |
|--------------------------------|---------|--------|-----------|---------------|-----------|--------------|------------------------------------|-----|
| STEEL                          |         |        |           |               |           |              |                                    |     |
| JDIA14                         | 81870   | 1/4-20 | 3/8       | 1             | 100       | 2.33         | 64.20/c                            |     |
| JDIA38                         | 81875   | 3/8-16 | 1/2       | 1 9/16        | 50        | 3.30         | 88.20/c                            |     |
| JDIA12                         | 81880   | 1/2-13 | 5/8       | 2             | 50        | 6.41         | 145.70/c                           |     |
| JDIA58                         | 81881   | 5/8-11 | 7/8       | 2 1/2         | 25        | 8.91         | 296.60/c                           |     |
| JDIA34                         | 81873   | 3/4-10 | 1         | 3 3/16        | 25        | 13.58        | 736.20/c NEW                       |     |
| STAINLESS STEEL 18-8 TYPE      |         |        |           |               |           |              |                                    |     |
| JDIA14SS                       | 81872   | 1/4-20 | 3/8       | 1             | 100       | 2.54         | PLEASE CALL FOR TRADE LIST PRICING |     |
| JDIA38SS                       | 81876   | 3/8-16 | 1/2       | 1 9/16        | 50        | 3.50         |                                    |     |
| JDIA12SS                       | 81883   | 1/2-13 | 5/8       | 2             | 50        | 6.25         |                                    |     |
| JDIA58SS                       | 81882   | 5/8-11 | 7/8       | 2 1/2         | 25        | 8.36         |                                    |     |
| NEW STAINLESS STEEL - 316 TYPE |         |        |           |               |           |              |                                    |     |
| JDIA141SS                      | 90345   | 1/4-20 | 3/8       | 1             | 100       | 2.54         | TRADE LIST PRICING                 | NEW |
| JDIA381SS                      | 90349   | 3/8-16 | 1/2       | 1 9/16        | 100       | 3.50         |                                    | NEW |
| JDIA121SS                      | 90353   | 1/2-13 | 5/8       | 2             | 50        | 6.03         |                                    | NEW |

## STEEL DROP-IN ANCHOR SETTING TOOL

FOR SETTING DROP-IN ANCHORS

Safety glasses should be worn for any driving applications.  
See our line of Safety Glasses Pages 220-222



| STOCK NO. | UPC NO. | SIZE   | WT. PER PKG. | STD. PKG. | SUGGESTED TRADE LIST PRICE PER |
|-----------|---------|--------|--------------|-----------|--------------------------------|
| DIA14T    | 12181   | 1/4-20 | 0.18         | 1         | 3.85/ea                        |
| DIA38T    | 12182   | 3/8-16 | 0.24         | 1         | 5.00/ea                        |
| DIA12T    | 12183   | 1/2-13 | 0.41         | 1         | 6.18/ea                        |
| DIA58T    | 12184   | 5/8-11 | 0.51         | 1         | 11.53/ea                       |
| DIA34T    | 17890   | 3/4-10 | 0.65         | 1         | 11.68/ea <b>NEW</b>            |