

Non-Metallic FR Series Device & Fixture Boxes

Extra-wide flanges prevent water and air intrusion, no need for gaskets or caulking. Use for mounting coach lights on stucco and/or flat siding. For new construction.

FEATURES AND BENEFITS

- Converts FAST for use on any cladding system up to 1-7/8"!
- Ships pre-assembled, ready for use with 1-3/8" finish or cladding thicknesses
- Easily converts for 5/8" finish thicknesses by removing back and reinstalling on the opposite side
- Add extension ring for 7/8" thickness
- Extra-wide flanges help meet the International Energy Conservation Code by creating a protective barrier against air and water infiltration. No gaskets or caulking required.
- Large 20 cubic inch volume
- Made of high strength polycarbonate
- Wall mount—one-piece design for new installations
- Up to a 10 lb fixture rating

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	APPLICATION	UNIT PKG	STD PKG	DIM A	DIM B	DIM C	DIM D
FR101F	12680	Device Box	10	10	7.875	7.125	3.750	3.525
FR405F	12681	Pan Box	10	10	6.750	6.750	4.000	1.375
FR420F	09615	Fixture Box	10	10	6.750	6.750	4.000	1.986








FR101F









INSTALLATION INSTRUCTIONS



For 5/8" wall finish thickness, loosen two screws and remove back.



Re-install the back on the OPPOSITE side of the box.



Assembled for 5/8" finish thickness.



For 7/8" wall finish thickness, install the the box. 1/4" extension ring



...to the front of

For New Construction Install FR series

box BEFORE




















ASSEMBLY OPTIONS

FR420F



Flange of box can be offset locating back panel to opposite side of box, as shown.