


Rigid/Intermediate Grade Conduit Fittings

Reducers & Plugs



CONDUIT REDUCERS – STEEL/IRON



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
Steel			
251	3/4" – 1/2"	50	4
252	1" – 1/2"	25	13
253	1 1/4" – 1/2"	10	30
254	1 1/2" – 1/2"	10	43
255	2" – 1/2"	5	83
260	1" – 3/4"	25	7
261	1 1/4" – 3/4"	10	23
262	1 1/2" – 3/4"	10	40
263	2" – 3/4"	5	79
268	1 1/4" – 1"	10	18
269	1 1/2" – 1"	10	27
270 S	2" – 1"	5	66
275	1 1/2" – 1 1/4"	10	13
276	2" – 1 1/4"	5	24
281	2" – 1 1/2"	5	27
Iron			
282	2 1/2" – 1"	10	120
283	2 1/2" – 1 1/4"	10	130
285	2 1/2" – 2"	10	150
288	3" – 1 1/2"	5	210
289	3" – 2"	2	160
290M	3" – 2 1/2"	5	120
291	3 1/2" – 2"	2	200
292	3 1/2" – 2 1/2"	2	225
293	3 1/2" – 3"	2	150
294	4" – 2"	2	270
295	4" – 2 1/2"	2	270
296	4" – 3"	2	260
297	4" – 3 1/2"	2	160
298	5" – 4"	1	385
299	6" – 5"	1	475

PLUGS – CAST IRON

Recessed



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
PLG1M	1/2"	50	6
PLG2M	3/4"	50	11
PLG3M	1"	25	22
PLG4M	1 1/4"	25	34
PLG5M	1 1/2"	10	48
PLG6M	2"	10	82
PLG7M	2 1/2"	2	150
PLG8M	3"	2	222
PLG9M	3 1/2"	1	340
PLG10M	4"	1	380

Square Head



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
PLG15M	1/2"	50	12
PLG25M	3/4"	50	16
PLG35M	1"	25	25
PLG45M	1 1/4"	25	34
PLG55M	1 1/2"	10	48
PLG65M	2"	10	80
PLG75M	2 1/2"	1	116
PLG85M	3"	1	185
PLG95M	3 1/2"	1	232
PLG105M	4"	1	310