

Non-Programmable Thermostat Selection Guide



	Model	Schedule Option	User Interface	Application					Power Method	Features and Functions					Display Information			Limited Warranty	Wiring Terminals	Replacements				
		Program Options		Stages	Gas, Oil or Electric	Heat Pump	Millivolt	Linevolt		Permanent Memory Retention	Selectable Auto or Manual Changeover	Comfort/Economy Mode	Temperature Setpoint Limits	Remote Locator	Display Size (Viewable)	On-Demand Backlighting	Simultaneous Display of Room and Set Temperatures			Honeywell	White-Rodgers	Robertshaw®	Toteline®	Other
 Wireless FocusPRO® 5000 Non-Programmable	TH5320R1002	Non-Prog	Soft Keys	Up to 3 Heat/2 Cool	•	•			Battery	•	•	•	•	•	5.09 sq. in.	•	•	5 Year	Wireless with Equipment Interface Module or Wireless Adapter					
 FocusPRO® 5000 Digital Non-Programmable	TH5110D1006	Non-Prog	Soft Keys	1 Heat/1 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	•		•		1.95 sq. in.	•	•	5 Year	R, Rc, W-O/B, Y, G, C	T8501, T8400, T8401	1F86	8400, 8401, 9400, 9401, 9550	P474-0100, P474-0130	
	TH5110D1022	Non-Prog	Soft Keys	1 Heat/1 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	•		•		2.98 sq. in.	•	•	5 Year	R, Rc, W-O/B, Y, G, C	T8501, T8400, T8401	1F86	8400, 8401, 9400, 9401, 9550	P474-0100, P474-0130	
	TH5220D1003	Non-Prog	Soft Keys	Up to 2 Heat/2 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	•	•	•		3.75 sq. in.	•	•	5 Year	R, Rc, W-O/B, AUX-W2, Y, Y2-E, L, G, C	T8501, T8511, T8524, T8400, T8401, T8411, T8424	1F73, 1F83, 1F86, 1F89	8400, 8401, 8425, 9400, 9401, 9415, 9420, 9550, 9555, 9560	P474-0100, P474-0130	
	TH5220D1029	Non-Prog	Soft Keys	Up to 2 Heat/2 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	•	•	•		5.09 sq. in.	•	•	5 Year	R, Rc, W-O/B, AUX-W2, Y, Y2-E, L, G, C	T8501, T8511, T8524, T8400, T8401, T8411, T8424	1F73, 1F83, 1F86, 1F89	8400, 8401, 8425, 9400, 9401, 9415, 9420, 9550, 9555, 9560	P474-0100, P474-0130	
	TH5320U1001	Non-Prog	Soft Keys	Up to 3 Heat/2 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	•	•	•		5.09 sq. in.	•	•	5 Year	R, Rc, W-O/B, W2-AUX/E, Y, Y2, G, L, C	T8501, T8511, T8524, T8400, T8401, T8411, T8424				
 PRO 3000 Non-Programmable	TH3110D1008	Non-Prog	Slide Switches	1 Heat/1 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	Manual				1.32 sq. in.	•	•	5 Year	R, Rc, C, W, O, B, Y, G	T8400, T8401	1F78-144	8400, 9500	P474-0130, P374-0200	Breabum 3000; LUX PDS100, PDS111, PDS150
	TH3210D1004	Non-Prog	Slide Switches	2Heat/1 Cool		•			Dual Powered (Battery and Hardwire)	•	Manual				1.32 sq. in.	•	•	5 Year	R, C, Y, Aux, O, B, E, G, L	T8411R	1F79-111	8425, 9420	P374-0300/SV300, P474-0100	Breabum 3200; LUX PSDH105, PSDH121
 PRO 1000 Non-Programmable	TH1110D1000	Non-Prog	Slide Switches	1 Heat/1 Cool	•	•	•		Dual Powered (Battery and Hardwire)	•	Manual				1.0 sq. in.	•		2 Year	R, C, W, O/B, Y, G	T8400, T8401	1F78-144	8400, 9500	P474-0130, P374-0200	Breabum 1000, 1005, 1010; LUX PDS100, PSD111, PSD150
	TH1210D1008	Non-Prog	Slide Switches	2 Heat/1 Cool		•			Dual Powered (Battery and Hardwire)	•	Manual				1.0 sq. in.	•		2 Year	R, C, W, O/B, Y, G	T8411R	1F79-111	8425, 9420	P374-0300/SV300, P474-0100	Breabum 1100, 1200; LUX PSDH105, PSDH121
 The Digital Round™	T8775A1009	Non-Prog	Dial	1 Heat	•*				Power Stealing	•					.75 sq. in.	•		5 Year	R, W	T87F				
	T8775C1005	Non-Prog	Dial	1 Heat/1 Cool	•	•			Power Stealing	•	Manual				.75 sq. in.	•		5 Year	R, Rc, W, O, B, Y, G	T87F				
 The Round™	T87K1007	Non-Prog	Dial	1 Heat	•*				Battery Assisted Power Stealing			50010944-001			N/A	•		5 Year	R, W	T87F				
	T87N1000	Non-Prog	Dial	1 Heat/1 Cool	•				Battery Assisted Power Stealing		Manual	50010944-001			N/A	•		5 Year	R, Rc, W, Y, G, O, B	T87F and Q539				
	T87N1026	Non-Prog	Easy-To-See™	1 Heat/1 Cool	•				Battery Assisted Power Stealing		Manual	50010944-001			N/A	•		5 Year	R, Rc, W, Y, G, O, B	T87F3467 and T87F5199				
 Mechanical	T834N1002	Non-Prog	Slide Switches and Lever	1 Heat/1 Cool	•				Mechanical		Manual	50019661-001			N/A			5 Year	R, Rc, W, Y, G, O, B	T834C	1E56, 1P56	9200, 400		
	T8034N1007	Non-Prog	Slide Switches and Lever	1 Heat/1 Cool	•				Mechanical		Manual	50019661-001			N/A			5 Year	R, Rc, W, Y, G, O, B	T8034C	1D56, 1F56	9200, 400		
 Mechanical	T822K1000	Non-Prog	Slide Switches and Lever	1 Heat	•*				Mechanical		Positive Off	50019661-001			N/A			5 Year	R, W	T822D	1E30	9204, 200		
	T822K1018	Non-Prog	Slide Switches and Lever	1 Heat	•*				Mechanical			50019661-001			N/A			5 Year	R, W	T822D	1E30	9204, 200		
	T827K1009	Non-Prog	Slide Switches and Lever	1 Heat			•*		Mechanical		Positive Off	50019661-001			N/A			5 Year	R, W	T827	1E30	9204, 400-404		
 Thermostat	TL7235A1003	Non-Prog	Horizontal Lays	1 Heat				•	208/240 V						2.67 sq. in.	•		5 Year	4 wire DPST					
 Thermostat	TL7230A1004	Non-Prog	Dial	1 Heat				•	208/240 V						N/A			5 Year	DPST					
 Thermostat	T410	Non-Prog	Dial	1 Heat				•	120/208/240/277 V						N/A				SPST or DPST					
 Thermostat	T4398	Non-Prog	Dial	1 Heat				•	120/208/240/277 V						N/A				SPST or DPST					

* Gas or oil heat only.