


B36RIC

6" Slope IC Remodel Housing

LAMP WATTAGE: (1) MAXIMUM 75W R/PAR30, 60W A19, 65W BR30



DESIGNED FOR 2" X 8" JOIST CONSTRUCTION



ITEM SELECTOR: (Please check the boxes below for the option desired)

TYPE	AIR-SHUT	TRIM TYPE	BAFFLE	REFLECTOR	TRIM/RING
B36RIC	<input type="checkbox"/> AT	<input type="checkbox"/> B391 <input type="checkbox"/> B392 <input type="checkbox"/> B602 <input type="checkbox"/> B646 <input type="checkbox"/> B663 <input type="checkbox"/> B673 <input type="checkbox"/> B601 <input type="checkbox"/> B601L <input type="checkbox"/> B605 <input type="checkbox"/> B605L	<input type="checkbox"/> W <input type="checkbox"/> P <input type="checkbox"/> SN <input type="checkbox"/> CP <input type="checkbox"/> BZ	<input type="checkbox"/> CL <input type="checkbox"/> RG <input type="checkbox"/> W <input type="checkbox"/> MB <input type="checkbox"/> BZ <input type="checkbox"/> CP <input type="checkbox"/> SN <input type="checkbox"/> SHZ	<input type="checkbox"/> WH <input type="checkbox"/> BK <input type="checkbox"/> SN <input type="checkbox"/> CP <input type="checkbox"/> CH <input type="checkbox"/> PB <input type="checkbox"/> BZ

Specifications:

B36RIC

AIR-SHUT	OPTION	TRIM TYPE	BAFFLE	REFLECTOR	TRIM/RING	GLASS
----------	--------	-----------	--------	-----------	-----------	-------

Sample of Catalog Number: B36RIC-AT-B391-W-WH

*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.

Catalog Number:

Project Name:

Note:

Type:

DESCRIPTION


Thermally protected, IC rated specification grade remodel recessed housing. For remodeling installations where housing will be in direct contact with insulation. Designed for sloped ceiling applications where the ceiling pitch ranges from 2/12 to 6/12. Accommodates up to 75W PAR30, R30 lamps, 60W A19 lamps and 65W BR30 lamps. Four remodel clips are easily retractable for fixture removal if necessary. Junction box is provided with eight 1/2" KOs and four Romex knockouts with strain relief."

SPECIFICATION

- HOUSING** - Die-formed, all aluminum construction for maximum heat dissipation and rust protection. "
- SOCKET** - Medium base screw shell porcelain socket preinstalled on a mounting bracket is specially designed to swivel and rotate so the lamp could be aligned properly. The lamp will aim straight down regardless of the ceiling pitch.
- INSTALLATION** - Four preinstalled spring clips which secure the housing firmly into ceiling to accommodate different ceiling thicknesses from 1/2" to 1-3/8" ."
- JUNCTION BOX** - through-branch cir-cuit wiring and has eight 1/2" KOs and four Romex knock-outs with strain relief. "
- THERMAL PROTECTION** - Standard thermal protection device guards against improper installation, over-lamping and misuse of insulation material."

FEATURES

- Thermally Protected IC Remodel housing.
- The socket bracket is specially designed to swivel and rotate so the lamp could be aligned properly. The lamp will aim straight down regardless of the ceiling pitch.
- Adjustable socket bracket with a slope indicator provides consistent lamp alignment and setup.



- Unit slips through 6-1/2" ceiling opening."
- Four Preinstalled spring clips which secure the housing firmly into ceiling and accommodate different ceiling thicknesses from 1/2" to 1-3/8" ."
- Wire through junction box.
- Can be installed from below the ceiling.
- Dependable, favorable design and effortless installation."
- 7-1/2" height allows use in 2" x 8" joist construction."
- Preinstalled socket cap provides electrical contact protection against dust, paint and over spray."

OPTIONS

AIR-SHUT

- Gasket to prevent air flow from heated or air conditioned spaces.
- Meets all national air flow requirements.

6" Slope Ceiling Incandescent Trims

(LAMP WATTAGE: (1) MAXIMUM 75W R/PAR30, 60W A19, 65W BR30)

Catalog Number:	
Project Name:	
Note:	Type:

B391CP-CP
METAL STEPPED BAFFLE R30/PAR30

BAFFLE FINISH:
W, P, SN, CP, BZ

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B394P-WH
PAR38/R40 STEPPED BAFFLE

BAFFLE FINISH:
W, P, SN, CP, BZ

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B392CL-WH
R30/PAR30 REFLECTOR

REFLECTOR FINISH:
CL, RG, W, MB, CP, SN, BZ

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B395CP-WH
R38/PAR40 REFLECTOR

REFLECTOR FINISH:
CL, RG, W, MB, CP, SN, BZ

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B601CP
METAL ALBALITE LENS

LENS:
ALBALITE

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B601L
PLASTIC ALBALITE LENS

LENS:
ALBALITE

TRIM/RING FINISH:
WHITE PLASTIC

B605PB
METAL FRESNEL LENS

LENS:
FRESNEL

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B605L
PLASTIC FRESNEL LENS

LENS:
FRESNEL

TRIM/RING FINISH:
WHITE PLASTIC

B663PB
PAR30 GIMBAL RING

TRIM/RING FINISH:
WH, BK, SN, CP, CH, PB, BZ

B673P-OV
PAR30 BAFFLE W/ GIMBAL RING

BAFFLE FINISH:
W, P, SN, CP

TRIM/RING FINISH:
WH

BAFFLE	REFLECTOR	TRIM RING
W White	CL Chrome	WH White
P Black	RG Gold	BK Black
SN Satin Nickel	W White	SN Satin Nickel
CP Copper	MB Black	CP Copper
BZ Bronze	CP Copper	CH Chrome
	SN Satin Nickel	PB Polish Brass
		BZ Bronze

*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.