

XP SERIES PORTABLE GENERATORS



Professional-grade for demanding job sites

XP SERIES PORTABLE GENERATORS 6,500 – 10,000 WATTS

The undisputed workhorse of the portable market, Generac's professional-grade XP Series portable generators are engineered specifically with contractors and construction sites in mind. All models are powered by the Generac OHVI® engine, built to withstand extended job site use.

WHAT'S INCLUDED

- Wheel Kit & Handles
- First Engine Oil Supply
- Maintenance Kit
- Starting Battery

Idle control reduces noise and conserves fuel for

extended run-times.



Easy access all-in-one control panel



How much power do you need?

How do you determine what size generator you need?

Sizing a portable generator is relatively easy. Check out this sample:

- Choose which devices you want to power at the same time.
- 2 Record and add the running watts listed for each device that you need to power.
- Record the starting watts listed for each device.
 Select the one device with the highest starting watts.
- Add that number to the the total running watts to determine the total wattage requirement.

Device	Running Watts	Additional Starting Watts	Generator Size
Paint Sprayer	600	1200	Minimum starting watts for your needs
Halogen Light	1000	0	1
Belt Sander	1200	2400	
Air Compressor -1/2HP	1000	2000	+
Total	3800	+ 2000	5800 starting watts

		Device	Running Watts	Additional Starting Watts	
	Jobsite	Air Compressor - 1 HP	1600	4500	
		Air Compressor - 1/2 HP	1000	2000	
		Airless Paint Sprayer- 1/3 HP	600	1200	
		Belt Sander - 3"	1200	2400	
		Bench Grinder - 8"	1400	1100	
		Circular Saw - 7-1/4"	1400	2300	
	eg.	Hand Drill - 1/2"	600	900	
	isq	Hand Drill - 3/8"	400	600	
	3	Miter Saw - 10"	1800	1800	
		Quartz Halogen Work Light	1000	-	
		Reciprocating Saw	960	-	
		Table Saw, 10"	2000	2000	
		Electric Hedge Trimmer	400	-	
		Electric Line Trimmer - 9"	350	-	
		Electric Chain Saw - 12" (1/2HP)	900	-	
		Computer with a 17" Monitor	800	-	
		Microwave - 1000 Watts	1000	-	
		Refrigerator/Freezer	700	2200	
		Sump Pump 1/2 HP	1050	2150	
	Pe	Television - 27"	500	-	
	set	Well Pump - 1/2 HP	1000	2100	
	훈	Central AC - 24,000 BTU	3800	4950	
		Furnace Fan Blower - 1/2 HP	875	2300	
		Heat Pump	4700	4500	
		Space Heater	1800	-	
		Window AC - 12,000 BTU	3250	3950	
		AM/FM Radio	100	-	
	tion	CD / DVD Player	100	-	
	rea	Cell Phone Battery Charger	25	-	
	Rec	Inflator Pump	50	150	
		RV Air Conditioner (13,500 BTU)	1500	700	
	* Watts listed are approximate. Check your appliance for actual require				

^{*} Watts listed are approximate. Check your appliance for actual requirements Total wattage requirements assumes intermittent starting of devices.

Portable Generator Specifications

Product Series	XP6500E	XP8000E	XP10000E
49-State Model Number	5930	5931	5932
CARB Model Number	5934	5935	N/A
Running Watts	6500	8000	10000
Starting Watts	8125	10000	12000
Engine Displacement	407cc	407cc	530cc
Engine Type	OHVI	OHVI	OHVI
Low Oil Shutdown	Yes	Yes	Yes
Starting Method	Electric/Recoil Pull Start (Battery Included)	Electric/Recoil Pull Start (Battery Included)	Electric (Battery Included)
Pressure Lube with Filter	Yes	Yes	Yes
Fuel Tank	Steel, 9 Gal.	Steel, 9 Gal.	Steel, 9 Gal.
Fuel Gauge	Yes	Yes	Yes
Run Time at 50%	11 Hours	10 Hours	9 Hours
Idle Control	On Control Panel	On Control Panel	On Control Panel
Total Harmonic Distortion	<5%	<5%	<5%
Hour Meter	Yes	Yes	Yes
Covered Outlets	Yes	Yes	Yes
Full Panel GFCI Protection - OSHA Compliant	Yes	Yes	Yes
GFCI Protected Outlets	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twistlock (1) 120/240V 30A L14-30R Twistlock	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twistlock (1) 120/240V 30A L14-30R Twistlock	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twistlock (1) 120/240V 30A L14-30R Twistlock (1) 125/240V 50A 14-50R Outlet
Handle Style	Folding/Locking	Fold/Locking	Folding Interlocked
Wheel Type	10" Solid High Density	10" Solid High Density	10" Solid High Density
Maintenance Kit Included	Yes	Yes	Yes
Dimensions (L" x W" x H")	34.6 x 29 x 27.2	34.6 x 29 x 27.2	34.75 x 29 x 34
Product Weight (49-State/CARB)	228/235	241/249	293
Warranty - Residential	3 Year Limited	3 Year Limited	3 Year Limited
Warranty - Commercial	2 Year Limited	2 Year Limited	2 Year Limited

All portable specifications and models subject to change. Please consult factory for availability.

HOME STANDBY GENERATORS

The Safe, Automatic Solution for Home Backup.

The power goes out and the generator goes on — whether you are home or away. It's that's simple. Install the #1 selling home standby generator from Generac and never again deal with extension cords or refuelling in a storm. Instead, enjoy safe, automatic



home protection from the inconveniences and potentially dangerous effects of power outages. There's nothing like the peace of mind a Generac automatic home standby generator can give to you and your family.

AUTOMATIC 24/7 POWER PROTECTION

Portable power since 1959

Since the original portable that started it all in 1959, Generac has continued to engineer advances in standby power for more than fifty years. Generac's product range includes power solutions from portable and automatic home standby generators to backup systems for commercial and industrial applications, all backed by an extensive nationwide service network of certified dealers. Because of our ongoing commitment to quality and innovation, Generac is the name home and business owners have come to trust.

Portable Parts and Service

Generac portable generators are supported through an extensive nationwide service network that provides parts and technical support to homeowners and contractors. For a portable generator dealer near you, visit generac.com.

