

Ratchet Cable Cutters

Choice of Insulated and Non-Insulated Grips

Simple one hand operation with a two speed ratcheting mechanism



45206I



45207I

Now with 1000V Insulated Handles

For many years the Greenlee 45206 and 45207 have set the standard for ratchet style cable cutters. They are the most dependable, longest lasting, easiest to use, and most comfortable cutters on the market. Now, Greenlee offers these same cutters with 1000V insulated handles. The new model numbers are 45206I and 45207I. These new cutters are tested to tough standards to assure they meet 1000V requirements. The 45206I and 45207I can easily be identified by their industry standard yellow and orange handles. These tools are not intended to be used on live circuits, but they provide an extra measure of protection for electrical workers.

All four of these cutters feature an exclusive “two-speed” cutting action. When the cutting is easy, the user opens the handles fully (two clicks) to get maximum cutting action per stroke, but when the cutting is difficult the user can open the handles partially (one click) to gain maximum cutting force. Also, all four cutters can be opened in the middle of the cutting cycle, and the ratcheting blade easily fits around cables in tight spaces.

Features

- Simple, one hand operation
- Exclusive two speed ratcheting mechanism adjusts for light/heavy cutting
- Well suited for tight working spaces
- Blades can be opened mid-cycle
- Available with cushioned handles or with 1000V insulated cushioned handles.

Capacity

Specifications	Copper	Aluminum	Comm. Cable
45206 & 45206I			
Maximum Capacity:	600 kcmil (MCM) (300 mm ²)	600 kcmil (MCM) (300 mm ²)	1-3/8" (35mm) diameter
Frequent Use Capacity:	500 kcmil (MCM) (240 mm ²)	500 kcmil (MCM) (240 mm ²)	
Length: 10" (254mm)			
Jaw Opening: 1-7/16" (36.5mm)			
45207 & 45207I			
Maximum Capacity:	750 kcmil (MCM) (400 mm ²)	1000 kcmil (MCM) (500 mm ²)	2" (51mm) diameter
Frequent Use Capacity:	600 kcmil (MCM) (300 mm ²)	750 kcmil (MCM) (400 mm ²)	
Length: 11" (279mm)			
Jaw Opening: 2" (51mm)			

Ordering Information

CAT#	UPC#	Description	Weight Lbs. (g)	Qty
45206	45206	Ratchet Cable Cutter	1.5 lbs. (0.7kg)	1
45206I	12680	Ratchet Cable Cutter with Insulated Handles	1.5 lbs. (0.7kg)	1
45207	45207	Ratchet Cable Cutter	2.4 lbs. (1.1kg)	1
45207I	12681	Ratchet Cable Cutter with Insulated Handles	2.4 lbs. (1.1kg)	1
45218	45218	Movable Blade (45206 & 45206I)	0.2 lbs. (0.1kg)	1
45212	45212	Fixed Blade and Handle (45206)	0.7 lbs. (0.3kg)	1
12526	12526	Fixed Blade and Handle (45206I)	0.7 lbs. (0.3kg)	1
45211	45211	Movable Blade (45207 & 45207I)	0.5 lbs. (0.2kg)	1
45228	45228	Fixed Blade and Handle (45207)	0.7 lbs. (0.3kg)	1
05883	05883	Fixed Blade & Handle (45207I)	0.7 lbs. (0.3kg)	1

DISTRIBUTOR INFORMATION :



45206



45206I



45207



45207I

USA
Tel: 800.435.0786
Fax: 800.451.2632

Canada
Tel: 800.435.0786
Fax: 800.524.2633

International
Tel: +1.815.397.7070
Fax: +1.815.397.9247