



Representative Login
 Telephone : 800-223-0853
 Fax : 704-633-3420

Home Applications Literature News Room Products Information Sales Team Warranty About Us



Single Pin Medium BiPin Recessed Double Contact

Choose Shat-R-Shield shatterproof lighting products for the ultimate in safety and reliability. Shat-R-Shield shatterproof / shatter-resistant T8 fluorescent lamps are coated from end-to-end with the patented, plastic safety coating. The coating reduces light output by only less than 1% and is a minimum of 16 mils thick. Most safety-coated fluorescent lamps feature uv-blocking protection -- antioxidants and ultraviolet stabilizers are present in most coatings to block UV emissions from 180 - 390 nanometers. If used properly under warranty criteria, the coating is guaranteed not to yellow, crack or flake for the rated-life of the lamp.

If a Shat-R-Shield fluorescent lamp is accidentally broken, virtually all glass, phosphors and mercury are safely contained within the clear and tough, skin-tight plastic coating. Shat-R-Shield shatterproof / shatter-resistant T5 fluorescent lamps are coated from end-to-end with the patented, plastic safety coating.

Don't see the lamp you need? Call Us Immediately

Watts	UPC Catalog Order #	Ordering Description	Std. Pkg. Qty.	Nominal Length (Inches)	CRI	Avg. Rated Life (Hours)	Mean Lumens
T8 Pre-Heat Safety-Coated Fluorescent Lamps (Philips)							
14	15282	F14T8/CW	24	15	62	7500	595
15	17016	F15T8/CW/ALTO	25	18	62	7500	765
15	17026*	F15T8/D/ALTO	25	18	79	7500	660
30	27016*	F30T8/CW/ALTO	25	36	62	7500	2000
T8 Safety-Coated Fluorescent (SRS)							
32	46820I	F32T8/841 Low Mercury	25	48	85	30000	2800
32	46821I	F32T8/850 Low Mercury	25	48	85	30000	2800
T5HO Safety-Coated Fluorescent (Shat-R-Shield) Min BiPin							
54	82549F	F54T5/841/HO	25	45.79		20000	4700
54	82559F	F54T8/850/HO	25	45.79		20000	4700
T8 Safety-Coated Fluorescent (Phillips)							
17	20498*	F17T8/TL730/ALTO	25	24	78	30000	1200
17	20508*	F17T8/TL735/ALTO	25	24	78	30000	1200
17	20518*	F17T8/TL741/ALTO	25	24	78	30000	1200
17	20530*	F17T8/TL835/ALTO	25	24	85	30000	1300
17	20540*	F17T8/TL841/ALTO	25	24	85	30000	1300
25	45498*	F25T8/TL730/ALTO	25	36	78	30000	1925
25	45502*	F25T8/TL735/ALTO	25	36	78	30000	1925
25	45538*	F25T8/TL835/ALTO	25	36	85	30000	2050
25	45542*	F25T8/TL841/ALTO	25	36	85	30000	2050
32	46496	F32T8/TL730/ALTO	25	48	78	30000	2660
32	46506	F32T8/TL735/ALTO	25	48	78	30000	2660
32	46516	F32T8/TL741/ALTO	25	48	78	30000	2660
32	46526	F32T8/TL830/ALTO	25	48	85	30000	2800
32	46536	F32T8/TL835/ALTO	25	48	85	30000	2800
32	46546	F32T8/TL841/ALTO	25	48	85	30000	2800
32	46823	F32T8/TL850/ALTO	25	48	82	30000	2710
32	46100	F32T8/TL930	25	48	95	20000	1860
32	46110	F32T8/TL950	25	48	98	20000	1860
40	47498	F40T8/TL730/ALTO	25	60	78	30000	3250
40	47528	F40T8/TL830/ALTO	25	60	86	30000	3500
40	47538	F40T8/TL835/ALTO	25	60	86	30000	3500
40	47546	F40T8/TL841/ALTO	25	60	86	30000	3500
T8 Plus Safety-Coated Fluorescent (Phillips)							
17	20521	F17T8/TL830/PLUS/ALTO	25	24	85	36000	925
32	46498	F32T8/TL730/PLUS/ALTO	25	48	78	36000	2660
32	46514	F32T8/TL741/PLUS/ALTO	25	48	78	36000	2660
32	46538	F32T8/TL835/PLUS/ALTO	25	48	85	36000	2800
32	46544	F32T8/TL841/PLUS/ALTO	25	48	85	36000	2800
32	46824	F32T8/TL850/PLUS/ALTO	25	48	82	36000	2710
32	46286	F32T8/TL865/PLUS/ALTO	25	48	82	36000	2610
T8 Plus SlimLine Safety-Coated Fluorescent (Phillips)							
59	43502	F96T8/TL735/PLUS/ALTO	25	96	78	30000	5190
59	43518	F96T8/TL741/PLUS/ALTO	25	96	78	30000	5190
59	43528	F96T8/TL830/PLUS/ALTO	25	96	86	30000	5490
59	43538	F96T8/TL835/PLUS/ALTO	25	96	86	30000	5490
59	43546	F96T8/TL841/PLUS/ALTO	25	96	86	30000	5490
T8 Octron Safety-Coated Fluorescent (Osram Sylvania)							

59	43498S*	F96T8/730/ECO	24	96	75	15000	5130
59	43508S*	F96T8/735/ECO	24	96	75	15000	5130
59	43518S*	F96T8/741/ECO	24	96	75	15000	5130
59	43528S*	F96T8/830/ECO	24	96	82	15000	5428
59	43538S*	F96T8/835/ECO	24	96	82	15000	5428
T8 Advantage Safety-Coated Fluorescent (Philips)							
32	46648	F32T8/ADV830/ALTO	25	48	85	36000	2950
32	46646	F32T8/ADV835/ALTO	25	48	85	36000	2950
32	46548	F32T8/ADV841/ALTO	25	48	85	36000	2950
32	46558	F32T8/ADV850/ALTO	25	48	82	36000	2875
32	46533	F32T8/ADV835/XEW/ALTO/25W	25	48	85	30000	2425
32	46618	F32T8/ADV841/XEW/ALTO/25W	25	48	85	30000	2425
32	46557	F32T8/ADV850/XEW/ALTO/25W	25	48	82	30000	2330
32	46641	F32T8/ADV830/XLL/ALTO/25W	25	48	85	40000	2330
32	46642	F32T8/ADV835/XLL/ALTO/25W	25	48	85	40000	2330
32	46643	F32T8/ADV841/XLL/ALTO/25W	25	48	85	40000	2330
32	46644	F32T8/ADV850/XLL/ALTO/25W	25	48	82	40000	2280
32	46645	F32T8/ADV830/EW/ALTO/28W	25	48	85	30000	2645
32	46647	F32T8/ADV835/EW/ALTO/28W	25	48	85	30000	2645
32	46540	F32T8/ADV841/EW/ALTO/28W	25	48	85	30000	2645
T8 Extra Long Life Safety-Coated Fluorescent (Philips)							
32	46615	F32T8/TL830/XLL/ALTO	25	48	85	40000	2800
32	46616	F32T8/TL835/XLL/ALTO	25	48	85	40000	2800
32	46617	F32T8/TL841/XLL/ALTO	25	48	85	40000	2800
T8 HO Safety-Coated Fluorescent (Philips)							
55	36548	F60T8/TL741/HO/ALTO	24	60	86	18000	4545
86	68547	F96T8/TL841/HO/PLUS/ALTO/TSC	25	96	86	30000	7625
T8 Safety-Coated Fluorescent (Osram Sylvania)							
13	14012S	F13T8/CW	24	12	60	7500	461
15	17035S	F15T8/D35	24	18	70	7500	846
15	17032S	F15T8/WW	24	18	52	7500	735
18	21303S	F18T8/CW/K24	24	24	60	7500	1035
30	27082S	F30T8/N	24	36	86	7500	1305
30	27033S	F30T8/WW	24	36	52	7500	1871
T8 Octron 700 Safety-Coated Fluorescent (Osram Sylvania)							
14	14508S	FO13/735/ECO	30	18	75	20000	745
17	20500S	FO17/735/ECO	30	24	75	20000	1170
25	45498S	FO25/730/ECO	30	36	75	20000	1755
32	46498S	FO32/730/ECO	30	48	78	25000	2520
32	46508S	FO32/735/ECO	30	48	78	25000	2520
32	46518S	FO32/741/ECO	30	48	78	25000	2520
32	46242S	FO32/750/ECO	30	48	78	25000	2385
32	46578S	FO32/765/ECO	30	48	78	25000	2430
40	47492S	FO40/730/ECO	30	60	75	20000	3150
40	47502S	FO40/735/ECO	30	60	75	20000	3150
T8 Octron 800 Safety-Coated Fluorescent (Osram Sylvania)							
17	20528S	FO17/830/ECO	30	24	82	20000	1240
17	20538S	FO17/835/ECO	30	24	82	20000	1240
25	45526S	FO25/830/ECO	30	36	82	20000	1975
25	45532S	FO25/835/ECO	30	36	82	20000	1975
32	46522S	FO32/830/ECO	30	48	85	35000	2802
32	46536S	FO32/835/ECO	30	48	85	35000	2802
32	46546S	FO32/841/ECO	30	48	85	35000	2802
T8 Octron 700 XP Safety-Coated Fluorescent (Osram Sylvania)							
25	45868S	FO25/735/XP/ECO	30	36	78	24000	1945
25	45878S	FO25/741/XP/ECO	30	36	78	24000	1945
32	46493S	FO32/730/XP/ECO	30	48	78	42000	2705
32	46503S	FO32/735/XP/ECO	30	48	78	42000	2705
T8 Octron 800 XP Safety-Coated Fluorescent (Osram Sylvania)							
17	20870S	FO17/830/XP/ECO	30	24	85	24000	1305
17	20838S	FO17/835/XP/ECO	30	24	85	24000	1305
17	20848S	FO17/841/XP/ECO	30	24	85	24000	1305
17	20898S	FO17/850/XP/ECO	30	24	85	24000	1305
17	20888S	FO17/865/XP/ECO	30	24	85	24000	1188
25	45828S	FO25/830/XP/ECO	30	36	85	24000	2065
25	45838S	FO25/835/XP/ECO	30	36	85	24000	2065
25	45848S	FO25/841/XP/ECO	30	36	85	24000	2065
25	45898S	FO25/850/XP/ECO	30	36	85	24000	2065
25	45888S	FO25/865/XP/ECO	30	36	85	24000	1900
25	46631S	FO32/25W/830/XP/SS/ECO	30	48	85	42000	2350
25	46632S	FO32/25W/835/XP/SS/ECO	30	48	85	42000	2350
25	46633S	FO32/25W/841/XP/SS/ECO	30	48	85	42000	2350
25	46634S	FO32/25W/850/XP/SS/ECO	30	48	85	42000	2280
28	69545S	FO28/830/XP/SS/ECO	30	48	85	42000	2590
28	69546S	FO28/835/XP/SS/ECO	30	48	85	42000	2590
28	69468S	FO28/841/XP/SS/ECO	30	48	85	42000	2590
28	69467S	FO28/850/XP/SS/ECO	30	48	80	42000	2470
30	27526S	FO30/830/XP/SS/ECO	30	48	85	42000	2710
30	27527S	FO30/835/XP/SS/ECO	30	48	85	42000	2710

	27546S	FO30/841/XP/SS/ECO	30	48	85	42000	2710
32	46523S	FO32/830/XP/ECO	30	48	85	42000	2850
32	46188S	FO32/835/XP/ECO	30	48	85	42000	2850
32	46466S	FO32/841/XP/ECO	30	48	85	42000	2850
32	46828S	FO32/850/XP/ECO	30	48	85	42000	2850
32	46888S	FO32/865/XP/ECO	30	48	85	42000	2708
32	46822S	FO32/850/XP/XL/ECO	30	48	80	40000	2813
40	47828S	FO40/830/XP/ECO	30	60	85	24000	3560
40	47536S	FO40/835/XP/ECO	30	60	85	24000	3560
40	47546S	FO40/841/XP/ECO	30	60	85	24000	3560
59	43828S	FO96/830/XP/ECO	24	96	85	18000	5795
59	43533S	FO96/835/XP/ECO	24	96	85	18000	5795
59	43848S	FO96/841/XP/ECO	24	96	85	18000	5795
T8 Octron 800 XPS Safety-Coated Fluorescent (Osram Sylvania)							
25	45839S	FO25/835/XPS/ECO	30	36	85	30000	2090
32	46547S	FO32/830/XPS/ECO	30	48	85	42000	2945
32	46549S	FO32/835/XPS/ECO	30	48	85	42000	2945
32	46548S	FO32/841/XPS/ECO	30	48	85	42000	2945
32	46550S	FO32/850/XPS/ECO	30	48	80	42000	2850
32	46551S	FO32/865/XPS/ECO	30	48	80	42000	2750

116 Ryan Patrick Drive, Salisbury, NC 28147 • Telephone: **US** (800) 223-0853 / (704) 633-2100 • **Canada** (800) 248-4911 • Fax: **US** (704) 633-3420

[Home](#) | [Applications](#) | [Literature](#) | [News Room](#) | [Products](#) | [Regulations](#) | [Sales Team](#) | [Warranty](#) | [Contact Us](#)

Copyright 2013 Shat-R-Shield, Inc. All Rights Reserved.