

# Safety Switches

## Accessories: NEMA Type 1 and 3R Enclosures

Spec-Setter™ Safety Switches

30-600 Amperes: TG and TH

800-1200 Amperes: TC

### Equipment Ground Kits

Ampere Rating	Wire Range		Standard Package	Product Number	List Price
	AWG/kcmil Copper	AWG/kcmil Aluminum			
30A	(4) 14-8, (3) 14-4	(4) 14-8, (3) 6-4	20	TGL1	\$6.75
60A					
100A	(3) 10-1/0	(3) 10-1/0	1	TNG3	\$60.00
200A					
600A	(3) 2-250	(3) 2-250	1	TGL6 <sup>1</sup>	\$68.25
400A					

<sup>1</sup>GO-131



TGL1 Equipment Ground Kit

### Neutral Kit Insulated, Groundable and Bondable

Ampere Rating	System Voltage	Fusible	Wire Range		Standard Package	Product Number	List Price
			AWG/kcmil Copper	AWG/kcmil Aluminum			
30A	240Vac					TNI21	\$50.75
30A	600Vac		12-2	12-2	1	TNI62 <sup>2</sup>	\$50.75
60A		Yes	12-2	12-2	1	TNIA62	\$50.75
100A		Yes	10-1/0	10-1/0	1	TNIA63	\$108.00
100A		No	10-1/0	10-1/0	1	TNI63 <sup>2</sup>	\$108.00
200A			2-250	2-250	1	TNIA64	\$132.00
400A			(1) 2-600 or (2) 1/0-250	(1) 2-600 or (2) 1/0-250	1	TNI65	\$232.00
400A			(1) 2-600 or (2) 1/0-250	(1) 2-600 or (2) 1/0-250	1	TNI65A	\$232.00
600A			(2) 4-500	(2) 4-500	1	TNI66	\$232.00
800A			(3) 2-600 or (6) 1/0-250	(3) 2-600 or (6) 1/0-250	1	TNI67	\$490.00
1200A			(4) 3/0-800	(4) 3/0-800	1	TNI68A	\$675.00

**Switching Neutral:** Order standard switch of required number of poles and use dummy fuse in neutral pole.

<sup>2</sup>Not suitable for type TG switches.



TNG3 Equipment Ground Kit

### Lug Wire Sizes Line and Load Terminal

Ampere Rating	Wire Range	
	AWG/kcmil Copper	AWG/kcmil Aluminum
30A (250V)	14-8	12-8
30A (600V)	12-2	12-2
60	12-2	12-2
100	10-1/0	10-1/0
200	2-250	2-250
400	(1) 2-600 or (2) 1/0-250	(1) 2-600 or (2) 1/0-250
600	(2) 4-500	(2) 4-500
800	(3) 2-600 or (6) 1/0-250	(3) 2-600 or (6) 1/0-250
1200	(4) 3/0-800	(4) 3/0-800



**Publications and Reference:** See Section 22 for a complete list of additional product-related publications