



*** 22471**
Mini Bi-Pin Quartz MR16 Socket
 GX5.3 Base
 12" 18 Gauge Leads
 SF-1 200° C Leads
 100 Watts Max., 250 Volts
 Height - 1"

*** 22470 - GY6.35 Base**
*** 22472 - GX5.3 Base**
Mini Bi-Pin Quartz MR16 Socket
 12" 18 Gauge Leads
 SF-1 200° C Leads
 100 Watts Max., 250 Volts
 Height - 3/8"

*** 22481**
High Pressure Sodium Lamp Socket
 9" Wire Leads
 Medium Base
 SF-2/SEW-2 200° Leads
 4 K.V. Pulse Rated
 660 Watts Max., 600 Volts
 1/2" Bushing
 Height - 1 1/4"

*** 22480**
High Pressure Sodium Lamp Socket
 9" Wire Leads
 Medium Base
 SF-2/SEW-2 200° Leads
 4 K.V. Pulse Rated
 660 Watts Max., 600 Volts
 1/2" Screw-Down
 Height - 1 1/4"



*** 11110**
Quartz Lamp Holder
 5" Wire Leads
 SF-1 200° C 300V Leads
 For 4 5/8" Lamp
 500 Watts Max.
 250 Volts
 Fits R7S, 4 5/8" Lamp Bases
 Height - 1 3/8"

*** 11112**
HQI Lamp Holder
 15" SF-2 200° C Leads
 1000 Watt Max.
 250 Volts
 For R7S Lamp Bases
 Height - 1 5/8"

*** 11109**
Quartz Lamp Holder
 5" Wire Leads
 SF-1 200° C
 500 Watts Max.
 250 Volts
 300 Volts Leads
 Fits R7S, 3 1/8" Lamp Bases
 Height - 1"

*** 11100**
Double Contact Bayonet Socket
 11" Wire Leads
 Threaded 1/8-IP
 SF-1 200° C 300V Leads
 150 Watts Max.
 125 Volts
 Height - 1 1/4"



*** 11104**
Porcelain Halogen Socket
 5" Wire Leads
 SF-1 200° C 300V Leads
 100 Watts Max., 250 Volts
 Fits G4, GX5.3, GV5.3
 and G6.35 Lamp Bases
 Height - 3/8"

*** 11107**
MR16 Porcelain Socket
 5" Wire Leads
 SF-1 200° C Leads
 75 Watts Max., 125 Volts
 Fits G5.3, GU5.3
 and GX5.3 Lamp Bases

*** 11108**
MR16 Porcelain Socket
 5" Wire Leads
 SF-1 200° C Leads
 75 Watts Max., 300 Volts
 Fits G5.3, GU5.3
 and GZ5.3 Lamp Bases

*** 11033**
Electronic Transformer
 Halogen
 Use with 12 Volt MR11 or MR16 Halogen Lamps
 Input 120 Volts AC
 Output 12 Volts, 80 Watt Max.
 3 1/2" White and 6" Black
 18 Gauge Leads

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com