



FRAME-IN KIT



REFLECTOR TRIM

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets							
	Open Downlight					Wall Washer	Open Wet Location	Enclosed Wet Location
2002P1	Specular Reflector	Cone	Satin Cone	Baffles	Pinhole			
	2045 2046 2046CD	2012 2012NM 2013 2013NM 2013BKNM 2013BK 2013CD 2013CDNM 2013WH	2008 2010NM 2010 2008NM	2005 2005BNM 2005NM 2005WH	2011	2095 2096 2096CD	2084CD 2084WH	2090

Features

- Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 4" x 3 1/2" x 2", .063" (#14 ga.) galvanized steel. U.L. listed for maximum of 8 No. 12 ga. 75° C through branch circuit conductors (60° C for end of run). Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** .059" (#16 ga.) galvanized steel. 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- Socket Housing:** Aluminum or galvanized steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Insulation must be kept 3" away from fixture sides and wiring compartments and must not be placed above fixture in a manner which will entrap heat.

Options & Accessories

- Mounting Bars:** 1964 - 20" set of (2)
- T-Bar Ceiling Clips:** 1956 - set of (4)
- Plaster Ceiling Ring:** 1960 - 7/8" depth for wet plaster ceilings.
- 277V Remote Step-Down Transformer:** 7997 - 277V down to 120V, 300W maximum load
- Extra Thick Ceiling Ring (2" max):** 1967C

Labels

UL (Suitable for Damp Locations), I.B.E.W.

Romex® is a registered trademark of General Cable Industries Inc.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	