


Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:

Lytening



Ceiling Cutout: 7" Diameter

Ordering guide Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

example: 1104SICR + B16

Frame-In Kit Series	Reflector Trims (See Individual Reflector Trim Specification Sheets)			
Catalog number	Open Downlights			
1104SICR LyteCaster 6 3/4" remodeler frame-in kit	Basic White	Baffles	Eyeball	Enclosed Diffusers
	B16	B17 B17WH		

* For Non-IC applications only.

Features

- Housing:** .032" (#20 ga.) Aluminum. UL listed convertible IC/NON-IC. Integral retaining spring secures housing to ceilings up to 2" thick. Removable for access to junction box and ceiling plenum. 5 1/2" tall for use in 2" X 6" joist construction and shallow plenum applications.
- Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032" (#22 ga.) galvanized steel. UL listed for 90°C supply wire. Suitable for branch circuit wiring supplying connected fixtures. Cable clamp permits attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 Volt 200°C) leads to junction box.
- Thermal Protector:** Meets NEC and U.L. requirements. Located inside housing.

Options and Accessories

AirSeal Kit: LASS6R
(Required for AirSeal installation)

Labels

UL (Type IC/NON-IC Convertible; Suitable for Damp Locations). Complies with Air Leakage Requirements stated in the Model Energy Code, California Title 24 and the Washington State Energy Code..

Romex is a registered trademark of General Cable Industries Inc.