

# GE OEM Load Center Parts Program

## PowerMark Plus™ & PowerMark Gold™ Load Center Selection Guide

### Three-Phase, Four-Wire, 208Y/120 Vac ①

#### OEM Interiors used in PowerMark Plus Load Centers

- Factory-Installed Main Lug Load Center Interiors
  - OEM interiors are UL-recognized components listed under UL file E21790

| Main Ampere Rating | Maximum Spaces |        |          | Total 1-Pole Spaces | Cat. No.     |  | Drawing Page-# |
|--------------------|----------------|--------|----------|---------------------|--------------|--|----------------|
|                    | 1" THQL        |        |          |                     | OEM-Interior | Complete-Load Center, Indoor Enclosure |                |
|                    | 1-pole         | 2-pole | 3-pole ② |                     |              |  |                |
| 100                | 3              | 1      | 1        | 3                   | 565B837G1    | —                                      | —              |
| 125                | 12             | 6      | 4        | 12                  | TL12412U     | TL12412C                               | 38             |
| 150                | 18             | 8      | 6        | 18                  | TL14815U     | TL18415C                               | 40             |
|                    | 24             | 12     | 8        | 24                  | TL24415U     | TL24415C                               | 42             |
| 200                | 18             | 8      | 6        | 18                  | TL18420U     | TL18420C                               | 44             |
|                    | 30             | 14     | 10       | 30                  | TL30420U     | TL30420C                               | 46             |
|                    | 42             | 20     | 14       | 42                  | TL42420U     | TL42420C                               | 48             |
| 225                | 30             | 14     | 10       | 30                  | TL30422U     | TL30422C                               | 50             |
|                    | 42             | 20     | 14       | 42                  | TL42422U     | TL42422C                               | 52             |

- Main Breaker–Style Load Centers
  - Main Lugs Not Included
  - OEM interiors are UL-recognized components listed under UL file E21790

| Main Ampere Rating | Maximum-Spaces |        |          | Total 1-Pole Spaces | Cat.-No.     |  | Drawing Page-# |
|--------------------|----------------|--------|----------|---------------------|--------------|--|----------------|
|                    | 1"-THQL        |        |          |                     | OEM-Interior | Complete-Load Center, Indoor Enclosure |                |
|                    | 1-pole         | 2-pole | 3-pole ② |                     |              |  |                |
| 100                | 12             | 6      | 4        | 12                  | TM12410U ③   | TM12410C                               | 54             |
|                    | 18             | 8      | 6        | 18                  | TM18410U ③   | TM18410C                               | 56             |
| 125                | 30             | 14     | 10       | 30                  | TM30412U ④   | TM30412C                               | 58             |
| 150                | 24             | 12     | 8        | 24                  | TM24415U ④   | TM24415C                               | 61             |
|                    | 30             | 14     | 10       | 30                  | TM30415U ④   | TM30415C                               | 64             |
|                    | 42             | 20     | 14       | 42                  | TM42415U ④   | TM42415C                               | 67             |
| 200                | 24             | 12     | 8        | 24                  | TM24420U ④   | TM24420C                               | 70             |
|                    | 30             | 14     | 10       | 30                  | TM30420U ④   | TM30420C                               | 73             |
|                    | 42             | 20     | 14       | 42                  | TM42420U ④   | TM42420C                               | 76             |
| 225                | 42             | 20     | 14       | 42                  | TM42422U ④   | TM42422C                               | 79             |

- ① Also UL Listed for 3-phase, 4-wire 240/120 Vac delta and 3-phase, 3-wire 240 Vac branch breakers installed.
- ② Three-pole plug-in breakers available through 100 amperes.
- ③ Main Breaker, THHQL32100 included.
- ④ For Main Breaker, order TQD\*X2 or THQD\*X2 style breaker with appropriate mounting bracket (see drawings).