



Complete Fixture consists of Frame-In Kit and Reflector Trim. Select each separately.

UniFrame™ Frame-In Kit	UniFrame™ Compact Fluorescent Performance Series Reflector Trims							
	Vertical Open	Vertical Wall Wash - Single	Vertical Wall Wash - Double	Horizontal Open	Horizontal Wall Wash - Single	Horizontal Wet Location Lensed / Diffused		Horizontal Cross Blade
<b>1001F13U</b> 13w Quad/Triple GX24q-1 Base 120v – 0.13amp max 277v – 0.06amp max  <b>1001F18U</b> 18w Triple GX24q-2 Base 120v – 0.17amp max 277v – 0.08amp max  <b>1001F26U</b> 26w Triple GX24q-3 Base 120v – 0.24amp max 277v – 0.11amp max	<b>1001CL</b> <b>1001CD</b> <b>1001WH</b>	<b>1001CLSW</b> <b>1001CDSW</b> <b>1001WHSW</b>	<b>1001CLDW</b> <b>1001CDDW</b> <b>1001WHDW</b>	<b>1001HCL</b> <b>1001HCD</b> <b>1001HWH</b>	<b>1001HCLSW</b> <b>1001HCDSW</b> <b>1001HWHSW</b>	Clear Lens <b>1001HCLC</b> <b>1001HCDC</b> <b>1001HWHC</b>  Opal Lens <b>1001HCLO</b> <b>1001HCDO</b> <b>1001HWHO</b>	Fresnel <b>1001HCLF</b> <b>1001HCDF</b> <b>1001HWHF</b>	<b>1001HACB</b> <b>1001HWHCB</b>
<b>Universal Series Reflector Trims</b> (Reference Trim Spec Sheet for Recommended Lamping)								
	Performance Cone	Cone	Satin Cone	Baffle	Wall Wash	Wet Location		
	1013CFL 1013CDCFL	1012* 1013* 1013BK* 1013WH 1013CD* 1071 1045 1046 1046CD	1008* 1010*	1005* 1005BNM 1005WH 1076 1076WH	1035 1035WH 1085 1095 1096 1096CD	1021** 1024 1078		

\*Add NM suffix to catalog number for Natural Metal flange and finish.

\*\*Only compatible with 13W and 18W Quad Lamps.

### Features

- Mounting Frame:** .036" (#20ga.) Galvanized Steel. Accommodates all ceilings up to 1 1/2" thick; including existing or inaccessible areas.
- Trim Clips:** "Push In / Twist Out" Stainless Steel clips hold reflector flush to ceiling.
- Junction Box:** 2" x 4" x 3-1/2" (22cu.in.) .032" (#22ga.) galvanized steel. UL Listed for maximum of 8 (#12ga.) through branch circuit conductors.
- UniFrame™ Mounting System – Grid Ceiling:** Tool free mounting in grid ceilings. .036" (20ga.) Galvanized Steel interlocking slide bars adjust to 24-1/8" long accommodating 24" O.C. Ceiling Grid. Adjustable speed clamps for positive attachment to grid ceiling systems.
- UniFrame™ Mounting System – Wood Joist Ceiling:** Integral nailing tabs, alignment guides, fastener holes and bendable strapping guides for wood joist installation. Galvanized Steel interlocking slide bars adjust from 12-15/16" to 24-1/8" long to accommodate 16" and 24" O.C. joist spacing, with or without strapping.
- Ballast:** 120V – 277V UL Listed Electronic Ballast, end of lamp life protection, class "P" thermally protected, class "A" sound rating.
- Socket:** Four-pin base, molded thermoplastic socket, prewired with No. 18 AWM leads to ballast.
- Socket Housing:** .036" (#20ga.) Galvanized Steel housing attaches to reflector trim by spring clip for precise optic alignment.

### Labels

**cULus Listed.** Suitable for Damp Locations. I.B.E.W.

### Accessories

1967B Extra Thick Ceiling Adapter (2" thk)

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710  
 We reserve the right to change details of design, materials and finish.  
 www.lightolier.com © 2008 Philips Group • C0708