

Pro-TermTM Terminals, Disconnects and Splices

Pro-TermTM General Purpose Terminals



- Styles: rings, forks, and locking forks
- Butted seam construction
- Low package quantity
- RoHS compliant material

Part Number Vinyl Insulated	Part Number Non-Insulated	Wire Range	Stud / Tongue Size	Std. Pkg. Qty.
--------------------------------	------------------------------	------------	--------------------	----------------

Ring Terminals

	E18-4RB-L	22-18 AWG	#4	50
EV18-6RB-L	E18-6RB-L		#6	50
EV18-8RB-L	E18-8RB-L		#8	50
EV18-10RB-L	E18-10RB-L		#10	50
EV18-14RB-L			1/4"	50
EV18-56RB-L			5/16"	50
	E14-4RB-L	16-14 AWG	#4	50
EV14-6RB-L	E14-6RB-L		#6	50
EV14-8RB-L	E14-8RB-L		#8	50
EV14-10RB-L	E14-10RB-L		#10	50
EV14-14RB-L			1/4"	50
EV14-56RB-L			5/16"	50
EV10-6RB-Q	E10-6RB-Q	12-10 AWG	#6	25
EV10-8RB-Q	E10-8RB-Q		#8	25
EV10-10RB-Q	E10-10RB-Q		#10	25
EV10-14RB-Q	E10-14RB-Q		1/4"	25
EV10-56RB-Q			5/16"	25
EV10-38RB-Q			3/8"	25

Fork Terminals

EV18-6FB-L	E18-6FB-L	22-18 AWG	#6	50
EV18-8FB-L	E18-8FB-L		#8	50
EV18-10FB-L	E18-10FB-L		#10	50
EV14-6FB-L	E14-6FB-L	16-14 AWG	#6	50
EV14-8FB-L	E14-8FB-L		#8	50
EV14-10FB-L	E14-10FB-L		#10	50
EV10-6FB-Q	E10-6FB-Q	12-10 AWG	#6	25
EV10-8FB-Q	E10-8FB-Q		#8	25
EV10-10FB-Q	E10-10FB-Q		#10	25
EV10-14FB-Q	E10-14FB-Q		1/4"	25

Locking Fork Terminals

EV18-6LFB-L	E18-6LFB-L	22-18 AWG	#6	50
EV18-8LFB-L	E18-8LFB-L		#8	50
EV18-10LFB-L	E18-10LFB-L		#10	50
EV14-6LFB-L	E14-6LFB-L	16-14 AWG	#6	50
EV14-8LFB-L	E14-8LFB-L		#8	50
EV14-10LFB-L	E14-10LFB-L		#10	50
EV10-6LFB-Q	E10-6LFB-Q	12-10 AWG	#6	25
EV10-8LFB-Q	E10-8LFB-Q		#8	25
EV10-10LFB-Q	E10-10LFB-Q		#10	25
EV10-14LFB-Q	E10-14LFB-Q		1/4"	25

Blade Terminals

EV18-145MB-L		22-18 AWG	.145 x .032 Tab	50
EV14-145MB-L		16-14 AWG	.145 x .032 Tab	50

Pin Terminals

EV18-P47B-L		22-18 AWG	0.07" Dia.	50
EV14-P47B-L		16-14 AWG	0.07" Dia.	50
EV10-P55-Q		12-10 AWG	0.10" Dia.	25

Pro-Term™ General Purpose Disconnects



- Styles: female, male, and piggyback
- Low package quantity
- RoHS compliant material

Part Number Nylon Fully Insulated	Part Number Vinyl Insulated	Part Number Non-Insulated	Wire Range	Tab Size (In.)	Std. Pkg. Qty.
--------------------------------------	--------------------------------	------------------------------	------------	-------------------	----------------

Female Disconnects

EDNF18-188FIB-L	EDV18-188B-L	ED18-188-L	22-18 AWG	.187 x .020	50
EDNF18-250FIB-L	EDV18-250B-L	ED18-250-L		.250 x .032	50
EDNF14-188FIB-L	EDV14-188B-L	ED14-188-L	16-14 AWG	.187 x .020	50
EDNF14-250FIB-L	EDV14-250B-L	ED14-250-L		.250 x .032	50
EDNF10-250FI-Q	EDV10-250-Q		12-10 AWG	.250 x .032	25

Male Disconnects

EDNF18250FIMB-L	EDV18-250M-L	ED18-250MB-L	22-18 AWG	.250 x .032	50
EDNF14250FIMB-L	EDV14-250M-L	ED14-250MB-L	16-14 AWG	.250 x .032	50
EDNF10250FIMB-Q	EDV10-250M-Q	ED10-250M-Q	12-10 AWG	.250 x .032	25

Piggyback Disconnects

	EDV18-250P-L		22-18 AWG	.250 x .032	50
	EDV14-250P-L		16-14 AWG	.250 x .032	50

Pro-Term™ General Purpose Splices and Wire Joints



- Styles: butt splices and wire joints
- Low package quantity
- RoHS compliant material

Part Number Nylon Insulated	Part Number Vinyl Insulated	Part Number Non-Insulated	Wire Range	Std. Pkg. Qty.
--------------------------------	--------------------------------	------------------------------	------------	----------------

Butt Splices

	ESV18BX-L	ES18B-L	22-18 AWG	50
	ESV14BX-L	ES14B-L	16-14 AWG	50
	ESV10BX-Q	ES10B-Q	12-10 AWG	25

Wire Joints

EJN218-216-L			22-14 AWG	50
EJN418-212-Q			18-12 AWG	25