



Landscape Lighting Stocking Guide

Philips Hadco

PHILIPS
HADCO



DISTRIBUTOR STOCK GUIDE

Philips is committed to providing our customers with the products they need when they need them. This stock guide contains hundreds of our best selling Philips luminaires and controls. Our commitment is to ship these items within 24-48 hours from the time the order is entered and received by our Philips warehouses.

Customer Service

Philips is putting our customers first. We will be the preferred lighting solutions partner by delivering innovative lighting solutions and providing an outstanding sales and service experience through a streamlined approach to our portfolio and our organization. For customers, our streamlined approach means orders for any brand or any product can be placed through one customer service department. This set-up improves our efficiency and increases our response time to our customers for quotations, order processing, technical support, warranties and more!

Philips Contact Center: 1-855-486-2216

Fax Orders: 1-800-519-2696

EDI is available to simplify your operations and improve efficiency.

Warehouse Legend and Stock Availability

Philips Lighting maintains stock levels of our lighting products in Carrollton, Texas (C) for the HADCO Landscape product line.

Stock orders for large quantities should be confirmed by customer service prior to order placement.

In order to avoid delays, it is recommended that stock orders be "stand alone" so that they may be shipped within the promised time-frame.

Terms and Conditions may vary by product family. Please consult your Philips sales representative for relevant warranty, freight claims, etc...

Our delivery promise is backed by a significant investment in finished goods and component inventory. If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs.

OUTDOOR



BEACONS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
-------	----------------	-------------	--------	------------	-----	---------------

Line Voltage

783352002266	I010-H	BEACON,120V	Bronze	C		
783352002280	I012-H	COMPOSITE BEACON,120V,100W,A19	Bronze	C		
783352006226	DWC2-A	SEMI-RECESSED,120V,20W,T3	Black	C		

Low Voltage

783352006233	DWCL1-A	MINI BEACON,COMPOSITE,20W,12V	Black	C		X
783352006240	DWCL2-A	SEMI-RECESSED,20W,12V,T3	Black	C		X



LARGE CLASSIC

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
-------	----------------	-------------	--------	------------	-----	---------------

Line Voltage

783352002341	I020-H	LARGE CLASSIC,120V,150W,PAR38	Bronze	C		
--------------	--------	-------------------------------	--------	---	--	--



ACCENT

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Line Voltage						
783352003485	BI-A	SMALL BULLET, I 20V, 100W, R20	Black	C		
783352003508	BI-G	SMALL BULLET, I 20V, 100W, R20	Verde	C		
783352003515	BI-H	SMALL BULLET, I 20V, 100W, R20	Bronze	C		
783352003539	BI-NL	SMALL BRASS BULLET W/ SHROUD, I 20, 100W	Natural Brass	C		
783352003577	B3-A	MEDIUM BULLET, I 20V, 100W, PAR/R30	Black	C		
783352003591	B3-H	MEDIUM BULLET, I 20V, 100W, PAR/R30	Bronze	C		
783352003614	B4-A	LARGE BULLET, I 20V, 300W, PAR38/R40	Black	C		
783352003645	B4-H	LARGE BULLET, I 20V, 300W, PAR38/R40	Bronze	C		
783352016935	B4-HLED18NFWL	LARGE BULLET, LED, NAR FLD, WARM	Bronze	C	LED	X
783352004994	BT5016-A	MICRO, BULLET, I 20V, 50W, MR16	Black	C		
783352017765	BT5016-ALED4NFW	MICRO, BULLET, I 20V, LED	Black	C	LED	X
783352005014	BT5016-H	MICRO, BULLET, I 20V, 50W, MR16	Bronze	C		
783352017727	BT5016-HLED7FLW	MICRO, BULLET, I 20V, LED	Bronze	C	LED	X
783352005052	BU1-A	SMALL, BULLET COMPOSITE, I 20V, 50W	Black	C		
783352005069	BU1-G	SMALL, BULLET COMPOSITE, I 20V, 50W	Verde	C		
783352005076	BU1-H	SMALL, BULLET COMPOSITE, I 20V, 50W	Bronze	C		
783352005083	BU3-A	MEDIUM BULLET, COMPOSITE, I 20V, 100W, PAR/R30	Black	C		
783352005090	BU3-G	MEDIUM BULLET, COMPOSITE, I 20V, 100W, PAR/R30	Verde	C		
783352005106	BU3-H	MEDIUM BULLET, COMPOSITE, I 20V, 100W, PAR/R30	Bronze	C		
783352005113	BU4-A	LARGE BULLET COMPOSITE, I 20V, 150W	Black	C		
783352005120	BU4-G	LARGE BULLET COMPOSITE, I 20V, 150W	Verde	C		
783352005137	BU4-H	LARGE BULLET COMPOSITE, I 20V, 150W	Bronze	C		

OUTDOOR



ACCENT

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Low Voltage						
783352019493	BLI-ALS7	BULLET,SMALL,12V,75W,MR16,LONG SHROUD	Black	C		
783352020116	BLI-HLS7	BULLET,SMALL,12V,75W,MR16,LONG SHROUD	Bronze	C		
783353020139	BLI-HSS7	BULLET,SMALL,12V,75W,MR16,SHORT SHROUD	Bronze	C		
783352004079	BL36S7-HL	BULLET,12V,PAR36,LAMP STAKE	Bronze	C		X
783352004154	BL5016-AS7	MICRO BULLET,12V,W/STAKE	Black	C		
783352002068	BL5016-AS7BAB	MICRO BULLET,12V,20W,W/STAKE	Black	C		X
783352017154	BL5016-AS7LED4NFW	MICRO BULLET,12V,4W,MR16,LED,STAKE	Black	C	LED	X
783352017079	BL5016-AS7LED7FLW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Black	C	LED	X
783352016997	BL5016-AS7LED7NFW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Black	C	LED	X
783352016959	BL5016-AS7LED7SPW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Black	C	LED	X
783352004222	BL5016-GS7BAB	MICRO BULLET,12V,20W,W/STAKE	Verde	C		X
783352004260	BL5016-HS7	MICRO BULLET,12V,W/STAKE	Bronze	C		
783352017161	BL5016-HS7LED4NFW	MICRO BULLET,12V,4W,MR16,LED,STAKE	Bronze	C	LED	X
783352017109	BL5016-HS7LED7FLC	MICRO BULLET,12V,7W,MR16,LED,STAKE	Bronze	C	LED	X
783352017093	BL5016-HS7LED7FLW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Bronze	C	LED	X
783352017024	BL5016-HS7LED7NFC	MICRO BULLET,12V,7W,MR16,LED,STAKE	Bronze	C	LED	X
783352017017	BL5016-HS7LED7NFW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Bronze	C	LED	X
783352016966	BL5016-HS7LED7SPW	MICRO BULLET,12V,7W,MR16,LED,STAKE	Bronze	C	LED	X
783354020145	BL711-AS7	BULLET,MICRO,12V,35W,MR11,STK	Black	C		X
783355020151	BL711-HS7	BULLET,MICRO,12V,35W,MR11,STK	Bronze	C		X

BULLET ACCESSORIES – BI ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352002389	IALO	LONG SHROUD,CLEAR LENS,BI	Black	C		
783352001542	IASO	SHORT SHROUD,CLR LENS,BI	Black	C		
783352002488	IHLC	LONG SHROUD CLEAR CONVEX LENS, BI	Bronze	C		
783352001559	IHLO	LONG SHROUD,FLAT CLR LENS, BI	Bronze	C		
783352002518	IHSO	SHORT SHROUD,CLR LENS,BI	Bronze	C		

BULLET ACCESSORIES – BUI ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352002587	IUALC	LONG SHROUD,W/CONVEX LENS,BUI	Black	C		
783352002594	IUALO	LONG SHROUD,W/FLAT LENS,BUI	Black	C		
783352002617	IUASO	SHORT SHROUD,W/FLAT LENS,BUI	Black	C		
783352002624	IUGLC	LONG SHROUD,W/CONVEX LENS,BUI	Verde	C		
783352002655	IUGSO	SHORT SHROUD,W/FLAT LENS,BUI	Verde	C		
783352002662	IUHLC	LONG SHROUD,W/CONVEX LENS,BUI	Bronze	C		
783352002679	IUHLO	LONG SHROUD,W/FLAT LENS,BUI	Bronze	C		
783352002693	IUHSO	SHORT SHROUD,W/FLAT LENS,BUI	Bronze	C		

OUTDOOR

BULLET ACCESSORIES – BU4 ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783356020167	4UALC	LONG SHROUD,W/CONVEX LENS,BU4	Black	C		
783352002969	4UASO	SHORT SHROUD,W/FLAT LENS,BU4	Black	C		
783352002976	4UGLC	LONG SHROUD,W/CONVEX LENS,BU4	Verde	C		
783352002983	4UGLO	LONG SHROUD,W/FLAT LENS,BU4	Verde	C		
783352003003	4UGSO	SHORT SHROUD,W/FLAT LENS,BU4	Verde	C		
783352003027	4UHSO	SHORT SHROUD,W/FLAT LENS,BU4	Bronze	C		



PATH LIGHTS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Line Voltage						
783352001603	MU5-G	MEDIUM MUSHROOM,120V,100W,A19	Verde	C		
783352007919	MU5-H	MEDIUM MUSHROOM,120V,100W,A19	Bronze	C		
783352007926	MU5-N	MUSHROOM,NATURAL BRASS,120V,100W	Natural Brass	C		
783352008589	P3-G	SMALL HORIZON,75W,120V,A19	Verde	C		
783352008909	R3-G	LONG HORIZON,75W,120V,A19	Verde	C		
783352012999	T39-G	LARGE TUDOR,120V,100W,A19	Verde	C		



PATH LIGHTS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Low Voltage						
783352019653	CPL12-AS7	CONTEMPORARY PATHLITE,STAKE,LAMP	Black	C		X
783352019660	CPL12-HS7	CONTEMPORARY PATHLITE,STAKE,LAMP	Bronze	C		X
783352019370	CUL14S7	COPPER PATHLYTE, 12V,20W,W/STAKE, LAMP	Copper	C		X
783352005748	CUL2S7	COPPER PATHLYTE, 12V,20W,W/STAKE, LAMP	Copper	C		X
783352005830	CUL6S7	COPPER PATHLYTE, 12V,20W,W/STAKE, LAMP	Copper	C		X
783352001955	CUL7S7	COPPER PATHLYTE, 12V,20W,W/STAKE, LAMP	Copper	C		X
783352005892	CUL9S7	COPPER PATHLYTE, 12V,20W,W/STAKE, LAMP	Copper	C		X
783352007674	MSL12-AS7	ADVENT PATH, 12"STEM,STAKE,LAMP	Black	C		X
783352007735	MSL18-AS7	ADVENT PATH, 18"STEM,STAKE,LAMP	Black	C		X
783352008046	MUL4-AS7	SMALL MUSHROOM,STAKE,LAMP	Black	C		X
783352008077	MUL4-GS7	SMALL MUSHROOM,STAKE,LAMP	Verde	C		X
783352002020	MUL4-HS7	SMALL MUSHROOM,STAKE,LAMP	Bronze	C		X
783352008237	MUL5-HS7	LARGE MUSHROOM,STAKE,LAMP	Bronze	C		X
783352001948	RL4-AS7	HORIZON,STAKE,LAMP	Black	C		X
783352009043	RL4-HS7	HORIZON,STAKE,LAMP	Bronze	C		X
783352019295	RL9-HS7	HORIZON,STAKE,LAMP	Bronze	C		X
783352019691	GAL3-ACS7	CONTEMPORARY PATHLYTE, 12W, 12V,W/ STAKE, LAMP	Copper	C		X
783352019868	TRL4-GS7	SMALL TUDOR, STAKE,LAMP	Verde	C		X
783352014139	TULI-GS7	SMALL TULIP PATHLYTE,STAKE LAMP	Verde	C		X

OUTDOOR

PATH LIGHTS ACCESSORY

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
-------	----------------	-------------	--------	------------	-----	---------------

Line Voltage


783352011992	S12G	12" STEM	Verde	C		
783352012074	S24G	24" STEM	Verde	C		






DECK LIGHTS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Low Voltage						
783352002099	DALI-A	DECKLYTE,ALUM,12V,10W,T3	Black	C		X
783352005915	DALI-B	DECKLYTE,ALUM,12V,10W,T3	White	C		X
783352001993	DALI-H	DECKLYTE,ALUM,12V,10W,T3	Bronze	C		X
783352002006	DALI-SS	DECKLYTE,SS,12V,10W,T3	Stainless Steel	C		X
783352006004	DCLI-N	DECKLYTE,CAST BRASS,12V,10W,T3	Natural Brass	C		X
783352006172	DULI-A	DECKLYTE,COMPOSITE,12V,10W,T3	Black	C		X
783352006196	DULI-H	DECKLYTE,COMPOSITE,12V,10W,T3	Bronze	C		X
783352006394	GACL2-AC	DECKLYTE,UP/DN,RD,COPR,12V,10W	Copper	C		X
783352002013	GADLI-AC	DECKLIGHT,COPPER,7.5W 12V 918	Copper	C		X
783352006400	GADL2-AC	DECKLYTE,COPPER,12V,12W,WEDGE	Copper	C		X
783352009081	RLLI-A	DECKLYTE,ALUM FACE,12V,12W,93	Black	C		X
783357020173	RLL2-PC	DECKLYTE,PC FACE,12V,12W,93	Copper	C		X
783352012791	SRL3-A	DECKLYTE 18W 12V W/1141 LAMP	Black	C		X
783352012821	SRL3-H	DECKLYTE 18W 12V W/1141 LAMP	Bronze	C		X
783352000316	SRL4-A	DECKLYTE,12V,10W XENON,T3	Black	C		X
783352000323	SRL4-B	DECKLYTE,12V,10W XENON,T3	White	C		X
783352000330	SRL4-G	DECKLYTE,12V,10W XENON,T3	Verde	C		X
783352000347	SRL4-H	DECKLYTE,12V,10W XENON,T3	Bronze	C		X
783352007322	LLL6-AC	LINELYTE,6"COPPER,XENON,12V	Copper	C		X



BOLLARDS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Line Voltage						
783352014825	DB14-H	BLLD,14"RD TOP,120V,100W,A19	Bronze	C		
783358020189	DB30-A	BLLD,30"RD TOP,120V,100W,A19	Black	C		
783352014832	DB30-H	BLLD,30"RD TOP,120V,100W,A19	Bronze	C		



DOWN LIGHT

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Low Voltage						
783352006080	DRL2-A	RD BKT DOWNLYTE 35W 12V MR16	Black	C		X
783352006486	GAHLI-AC	DOWNLYTE,SMALL,COPR,12V,27W,1156	Copper	C		X



INGROUND

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Line Voltage						
783352006691	I2G-H	INGROUND W/GUARD 100W 120V R30	Bronze	C		
783352006707	I2-H	INGROUND W/RING 100W 120V R30	Bronze	C		
783352006714	I3G-H	INGRND,W/GRD,120V,100W,PAR/R30	Bronze	C		
783352006721	I3-H	INGRND,W/RING,120V,100W,PAR/R30	Bronze	C		
783352007223	IT216G-H	INGRND W/TRANSFORMER GUARD, 120V, 75W MR16	Bronze	C		




INGROUND

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Low Voltage						
783352000125	IL116G-H	INGROUND W/GUARD 75W 12V MR16	Bronze	C		
783352000132	IL116-H	INGROUND W/RING 75W 12V MR16	Bronze	C		
783352000149	IL336-A	WELLYTE 50W 12V PAR36	Black	C		
783352000156	IL336-AL	WELLYTE 20W 12V W/PAR36 LAMP	Black	C		X
783352007254	IUL516-H	COMPOSITE INGROUND,12V,35W	Bronze	C		
783352019202	IUL516-HLED4NFW	INGROUND,LED	Bronze	C	LED	X


INGROUND ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
I2 Accessory						
783352000392	CP2	CONCRETE POUR ACCESS I2		C		
IL336 Accessory						
783352000453	IG3H	ROCK GUARD W/LENS - IL336		C		
783352000460	IL3H	LENS GUARD IL336		C		



JUNCTION BOX

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352001573	BI3	CAST IRON J-BOX,(6) 1/2"NPT		C		
783352003706	BI4	CAST IRON J-BOX,(4) 1/2"NPT		C		



STEP LIGHTS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
Line Voltage						
783352010728	RSC2AK5F13E	LVR BRICKLYTE, 13W,PLC13	Black	C		
783352010766	RSC2AK5IE	LVR BRICKLYTE, 120V,40W,T10	Black	C		
783352010940	RSC2HK5F13E	LVR BRICKLYTE, 120V,13W,PLC13	Bronze	C		
783352010995	RSC2HK5IE	LVR BRICKLYTE 120V 40WT10	Bronze	C		
Low Voltage						
783352011459	RSCL2HK5812	LOUVER BRICKLYTE	Bronze	C		


STEP LIGHTS ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352010094	RS2-AHO	HSG ONLY FOR RSB2/RSC2/RSF2	Black	C		
783352010117	RS2-HHO	HSG ONLY FOR RSB2/RSC2/RSF2	Bronze	C		
783352001979	MAKM	MASONRY KIT FOR STEPLYTES		C		



UNDERWATER LIGHT

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352014337	UWUL516-H	UNDERWATER,MICRO,12V,50W,MR16	Bronze	C		
783352019271	UWUL516-HLED4N-FW	MICRO U'WATER,LED	Bronze	C	LED	



WALL WASHER

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783361020213	WAML14F-HS720T3	MINI FLOOD,W/20W,T3 LAMP STK	Bronze	C		

ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783359020195	IAS16	LINEAR SPREAD LENS,MRI16		C		
783352000439	ICG16	CUT-OFF GRILLE FOR MRI16		C		
783352007209	ISL16	SPREAD LENS		C		
783352002037	LVC3	LOW VOLTAGE CONNECTOR		C		
783352007360	LVC4	LOW VOLTAGE CONNECTOR		C		
783352007407	MA22	SILIC FILLED WIRE NUTS,25/BX		C		
783352001757	MC1A	MOUNTING CANOPY	Black	C		
783352007490	MC1H	MOUNTING CANOPY	Bronze	C		
783352007605	MPLLL	MOUNTING PLATE,LLL,MASONRY		C		
783352011978	S1	ALUM IN-GROUND STAKE		C		
783352012128	S35B	PERMA POST 3-1/2"OD WHT	White	C		
783352012203	S3A	PERMA POST,3"OD,BLACK	Black	C		
783352012227	S3G	PERMA POST,3"OD,VERDE	Verde	C		
783352012234	S3H	PERMA POST,3"OD,BRONZE	Bronze	C		
783352012241	S3N	PERMA POST 3IN OD,BRASS CAP	Natural Brass	C		
783352012319	S6	LOW VOLT TELESCOPING PVC STAKE		C		
783352001825	S7	STAKE,MTG,12V,ARROW,12PK		C		
783352012340	S8	STAKE,MTG,12V,LONG ARROW,12PK		C		
783352013668	TM1H	TREE MOUNT ADAPTER	Bronze	C		
783352001726	TM2H	TREE MOUNT JUNCTION BOX	Bronze	C		
783352001733	TMC2H	TREE MT JUNCTION BOX,COMPOSITE SITE	Bronze	C		
783352013729	TMS10	TREE MOUNT STRAP		C		

TRANSFORMERS

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352013224	TBC303-15	INGR,T'FORMER,300W,QT,W/BREAKR		C		
783352013248	TBC603-15	INGR,T'FORMER,600W,QT,W/BREAKR		C		
783352015037	TC152-12	150VA/150W TRANSFORMER (SGL)		C		
783352015044	TC152-12TP	150VA-150W TFORMER W/EYE+TIMER		C		
783352015051	TC354-15	T'FORMER,300VA/300W,HINGD DOOR	Grey Painted	C		
783352015068	TC654-15	T'FORMER,600VA/600W,HINGD DOOR	Grey Painted	C		
783352015075	TC954-15	T'FORMER,900VA/900W,HINGD DOOR	Grey Painted	C		
783360020207	TS375-12	PERMA-POST W/INTEGRAL T'FORMER		C		
783352015006	TSS354-15	T'FORMER,300VA/300W,HINGD DOOR	Stainless Steel	C		
783352015013	TSS654-15	T'FORMER,600VA/600W,HINGD DOOR	Stainless Steel	C		
783352015020	TSS954-15	T'FORMER,900VA/900W,HINGD DOOR	Stainless Steel	C		

TRANSFORMERS ACCESSORIES

UPC #	Catalog Number	DESCRIPTION	FINISH	STOCKED IN	LED	LAMP INCLUDED
783352001818	PC3	PLUG-IN PHOTO CELL,DIRECT MT		C		
783352001665	T5	PLUG-IN TIMER,ANALOG		C		
783352001672	T6	PLUG-IN TIMER,DIGITAL		C		



Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216
www.philips.com



© 2013 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice. 10/13