

COMPUTER CABLES

Stranded Multi-Conductor
Overall Aluminum Shield
S-R Insulation -300 Volt



CONSTRUCTION	
Conductor	- tinned copper
Insulation	- SR-PVC with cabled Conductors
Shield/Drain	- Aluminum-polyester shield - Tinned copper drain wire with 100% shield coverage
Jacket	- Gray PVC

Standards:

- UL 444
- UL 758
- UL 1581
- NEC Article 800
- UL Rated -80C
- Voltage: UL 300 Volt

Part #	AWG	Conductors	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
D22004	20	4	7x8 TC	.010"	.032"	.231"	31.7
D22006	20	6	7x8 TC	.013"	.032"	.276"	52
D22008	20	8	7x8 TC	.013"	.032"	.248"	50.6
D22010	20	10	7x8 TC	.010"	.032"	.264"	60
D22012	20	12	7x8 TC	.010"	.032"	.283"	69.6
D22015	20	15	7x8 TC	.016"	.032"	.393"	105

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

COLOR CODE CHART

Cond. #	Color
1	Black
2	Red
3	White
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow
9	Purple
10	Gray
11	Pink
12	Tan
13	Red/Black Stripe
14	White/Black Stripe
15	Green/Black Stripe