



# Hex Head Tap Bolts Zinc Plated - PC 4090

Fully threaded hex head tap bolts. Made from grade 2 low carbon steel. Length is determined from the base of the fastener head. Continuous thread allows for take up adjustment. (MACHINE BOLTS)

- Hex Head Tap Bolts
- Full Thread
- Grade 2
- Zinc Plated Steel

CAT NO	UPC	SIZE	HEX SIZE	STD	MSTR	WT/STD	UNIT
MB1412	58700	1/4 x 1/2	7/16"	100	1000	1.18#	C
MB1434	58702	1/4 x 3/4	7/16"	100	1000	1.44#	C
MB141	58704	1/4 x 1	7/16"	100	1000	1.67#	C
MB14114	58706	1/4 x 1-1/4	7/16"	100	1000	2.01#	C
MB14112	58708	1/4 x 1-1/2	7/16"	100	1000	2.36#	C
MB142	58710	1/4 x 2	7/16"	100	1000	3.07#	C
MB14212	58712	<b>1/4-20</b> 1/4 x 2-1/2	7/16"	100	1000	3.75#	C
MB143	58714	1/4 x 3	7/16"	100	1000	4.35#	C
MB14312	58716	1/4 x 3-1/2	7/16"	100	1000	5.10#	C
MB144	58718	1/4 x 4	7/16"	100	1000	5.75#	C
MB14412	58720	1/4 x 4-1/2	7/16"	100	1000	6.36#	C
MB145	58722	1/4 x 5	7/16"	100	400	6.92#	C
MB14512	58724	1/4 x 5-1/2	7/16"	100	400	7.74#	C
MB146	58726	1/4 x 6	7/16"	100	400	8.39#	C
<hr/>							
MB51612	58750	5/16 x 1/2	1/2"	100	1000	1.95#	C
MB51634	58752	5/16 x 3/4	1/2"	100	1000	2.33#	C
MB5161	58754	5/16 x 1	1/2"	100	1000	2.74#	C
MB516114	58756	5/16 x 1-1/4	1/2"	100	1000	3.23#	C
MB516112	58758	5/16 x 1-1/2	1/2"	100	1000	3.82#	C
MB5162	58760	5/16 x 2	1/2"	100	1000	4.82#	C
MB516212	58762	<b>5/16-18</b> 5/16 x 2-1/2	1/2"	100	1000	5.95#	C
MB5163	58764	5/16 x 3	1/2"	100	1000	6.91#	C
MB516312	58766	5/16 x 3-1/2	1/2"	50	500	3.60#	C
MB5164	58768	5/16 x 4	1/2"	50	500	4.12#	C
MB516412	58770	5/16 x 4-1/2	1/2"	50	500	4.41#	C
MB5165	58772	5/16 x 5	1/2"	50	200	5.54#	C
MB516512	58774	5/16 x 5-1/2	1/2"	50	200	6.15#	C
MB5166	58776	5/16 x 6	1/2"	50	200	6.63#	C
<hr/>							
MB3812	58800	3/8 x 1/2	9/16"	100	1000	2.93#	C
MB3834	58802	3/8 x 3/4	9/16"	100	1000	3.55#	C
MB381	58804	3/8 x 1	9/16"	100	1000	4.03#	C
MB38114	58806	3/8 x 1-1/4	9/16"	100	1000	4.48#	C
MB38112	58808	3/8 x 1-1/2	9/16"	100	1000	5.54#	C
MB382	58810	3/8 x 2	9/16"	100	1000	6.94#	C
MB38212	58812	<b>3/8-16</b> 3/8 x 2-1/2	9/16"	100	500	7.80#	C
MB383	58814	3/8 x 3	9/16"	100	500	9.03#	C
MB38312	58816	3/8 x 3-1/2	9/16"	50	500	5.10#	C
MB384	58818	3/8 x 4	9/16"	50	500	6.53#	C
MB38412	58820	3/8 x 4-1/2	9/16"	50	500	7.21#	C
MB385	58822	3/8 x 5	9/16"	50	200	7.98#	C
MB38512	58824	3/8 x 5-1/2	9/16"	50	200	8.30#	C
MB386	58826	3/8 x 6	9/16"	50	200	8.74#	C
<hr/>							
MB1234	58850	1/2 x 3/4	3/4"	50	500	4.05#	C
MB121	58852	1/2 x 1	3/4"	50	500	4.36#	C
MB12114	58854	1/2 x 1-1/4	3/4"	50	500	4.69#	C
MB12112	58856	1/2 x 1-1/2	3/4"	50	500	6.50#	C
MB122	58858	1/2 x 2	3/4"	50	500	6.73#	C
MB12212	58860	1/2 x 2-1/2	3/4"	50	200	8.02#	C
MB123	58862	<b>1/2-13</b> 1/2 x 3	3/4"	50	200	9.37#	C
MB12312	58864	1/2 x 3-1/2	3/4"	50	200	10.75#	C
MB124	58866	1/2 x 4	3/4"	25	100	6.02#	C
MB12412	58868	1/2 x 4-1/2	3/4"	25	100	6.65#	C
MB125	58870	1/2 x 5	3/4"	25	100	7.40#	C
MB12512	58872	1/2 x 5-1/2	3/4"	25	100	8.10#	C
MB126	58874	1/2 x 6	3/4"	25	100	8.78#	C

