

AMERICAN FITTINGS Corporation



Made in the USA Since 1946

EMT CONDUIT

EMT Coupling: Compression Type / Raintight
Size Range: 1/2" to 4"

EMT Couplings Compression Type/Raintight

- RAIN AND CONCRETE TIGHT 1/2" to 4"
- For use in wet locations to ground and secure EMT raceway boxes and enclosures together
- Coupling utilizes two sealing rings to prevent water seepage
- Screw machined steel, zinc plated *



E101868

SPEC-grade



Featuring:
EZ-Torque Compression Nut

EMT Couplings - Raintight (EC-RT)

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
EC760USRT	1/2"	50	250	8
EC761USRT	3/4"	25	125	13
EC762USRT	1"	20	100	19
EC763USRT	1-1/4"	5	50	30
EC764USRT	1-1/2"	5	25	46
EC765USRT	2"	5	25	60
EC766USRT	2-1/2"	-	5	333
EC767USRT	3"	-	3	367
EC768USRT	3-1/2"	-	3	426
EC769USRT	4"	-	2	523

* Fittings 2 1/2" & Larger May Be Steel or Malleable Iron

Dimensional Table

Cat. #	A Length	B Diameter
EC760USRT	1.688	1.250
EC761USRT	2.000	1.563
EC762USRT	2.125	1.813
EC763USRT	3.063	2.188
EC764USRT	3.125	2.438
EC765USRT	3.375	2.938