
## Accessories

## **Clock Hanger**



3 Wire with 6" Leads Recept. UL listed 15A-125V Rating

	Pa (3W	RAYED LUMI- NUM ainted Steel IIHPSL)	(3	ALU- MINUM (.040") Satin Finish WIHPSAL)	ALU- MINUM (.050") Clear Anodized (3WIHP5AA) 40588	Steel Polished (3WIHPCA		
	STAIN- LESS TYPE 430		STAIN- LESS TYPE 302		SOLID BRASS	SOLID BRONZE (.040")		
	Satin Finish (3WIHPSS)		Spec. Grade Satin Finish (3WIHP302SS)		Satin Finish US#4 (3WIHP4BB)	Satin Finish US#10	BR)	
	40590		40591		40592	40595		
SPRAYED BRASS		IVORY SEMI- GLOSS		WHITE SEMI- GLOSS	WHITE	BROWN WRINKLE	IVORY WRINKLE	
Painted Steel (3WIHPBA)		Painted Steel (3WIHPIA)		Painted Steel (3WIHPWA)	Painted Steel (3WIHPDW)	Painted Steel (3WIHPDB)	Painted Steel (3WIHPDI)	
40580		40581		40582	40583	40584	40585	

## 0 = 0

## **ENERGY SAVING INSULATING GASKETS**

**Comply With Current Code Requirements** Mulberry's energy saving gaskets prevent the loss of heat and cold through outlets and switches located on outside walls. Constructed of UL listed cross link, close cell polyethylene insulating foam, they are available for single gang switch and duplex receptacles. Easy to install, they can be ganged by trimming or overlapping.



#40671 1 Toggle Switch



#40601



#40635

1 Duplex Receptacle 1 GFI Receptacle

Box Carton 50 500