

## **NEW PRODUCT ANNOUNCEMENT**

## **LEDUR** LED Under Cabinet

**Edge-Lit Technology** 120V Integral Dimmable Driver

90+ CRI

LEDUR LED Under Cabinet lights utilize edge-lit technology, eliminating the diode image and providing smooth, uniform reflectance of light without the hot spots generated by direct view mounted LEDs. Excellent for undercabinet lighting over granite, polished stone, quartz or any reflective surface. The LEDUR mounts quickly with captives screws and electrical quick connects. Completely dimmable and linkable the LEDUR is available in various lengths and in 2700K, 3000K and 4000K temperatures at 350+ lumens per foot and 90+ CRI.



- · Edge-lit design eliminates diode image
- · Excellent color rendition 90+ CRI
- · 350+ Lumens and 7 Watts per foot average
- · Exceeds California Title 24 high efficacy requirements
- · 2700K, 3000K (Warm) and 4000K (Cool) color temps
- · Available in 5 lengths from 8-3/4" to 32-3/4"
- · Low 1" depth by 3-1/2" width
- · Dark Bronze or White finish
- · Frosted Lens
- · Built-in On/Off switch
- · 120V Dimmable
- · Linkable up to 400 Watts
- · 3-Wire grounded electrical port on both ends for power or linking
- · Can be directly hardwired with Romex<sup>™</sup> feed
- Each unit includes Romex<sup>™</sup> Connector and End-to-End Connector
- · Includes Stab-In quick connectors
- · Easy to mount with captive screws
- · Integral electronic driver
- · 50,000 hours rated lamp life



















## **LEDUR** LED Edge-Lit Under Cabinet and Accessories



LEDUC LED UNDER CABI	NET LIGH	IT		
CATALOG NO.	LENGTH	WATTAGE	COLOR TEMP	FINISH
NUD-8808(temp)(finish)	8"	4.5W	<b>/27</b> 2700K	<b>BZ</b> Bronze
NUD-8811(temp)(finish)	11"	6.7W	/30 3000K WH /40 4000K 4000K available in White finish	WH White
NUD-8818(temp)(finish)	18"	11W		
NUD-8822(temp)(finish)	22"	12W		
NUD-8832(temp)(finish)	32"	16W	only	

Example: NUD-8832/30WH- 32" LEDUR Under Cabinet Light, Warm 3000K, White finish



J-Box for LEDUR Series

NUA-802 B or W

Hardwire box used to power NUD-8800 Series using Jumper Cables or NUA-804 Hard wire connector. L: 4" W: 1-3/4" H: 1"



End to End Connector for LEDUR Series

NUA-803 B or W

Used to seamlessly join two NUD-8800 LED fixtures. 3-Wire grounded connector. One included with each LEDUR unit



Jumper Cable for LEDUR Series

NUA-806 6" B or W NUA-812 12" B or W NUA-824 24" B or W NUA-872 72"  $\mathsf{B}\,\mathsf{or}\,\mathsf{W}$ 

Used to join NUD-8800 Series LED fixtures together or to an NUA-802 J-box.

3-wire grounded cables.



72"Hardwire Connector for LEDUR Series

NUA-804 B or W

3-Wire grounded connector/ cable used to hardwire NUD-8800 Series LED fixture to NUA-802 or J-Box.



72" Cord and Plug for LEDUR Series

NUA-805 B or W

Converts NUD Series LED fixtures from hardwire to direct plug-in units using connector pins on end of NUD unit. Grounded plug.

## **LEDUR SERIES** Sample Layouts

	DESCRIPTION	ITEM NO.
Α	NUD Series J-Box	NUA-802
В	End to End Connector (1 included with each LEDUR)	NUA-803
C	Hard-Wire Connector	NUA-804
D	Power Cord & Plug	NUA-805
E	6" Jumper Cable 12" Jumper Cable 24" Jumper Cable 72" Jumper Cable	NUA-806 NUA-812 NUA-824 NUA-872
F	LEDUR LED	NUD-88 Series

