

SECURITY AND ALARM CABLE

CL3R/CMR -Nonshielded Conductors

PVC Insulation & Jacket

300 Volt -22 AWG & 20 AWG



CONSTRUCTION

Conductor	- Stranded bare copper to ASTM B-3, B-8, and B-286
Insulation	- Color coded PVC
Jacket	- Gray PVC - Includes ripcord

Applications:

- Power limited control circuits
- Wiring of the following systems: Intercom, Security, Audio
- Suggested Voltage Rating: 300 Volts

Standards:

- NEC Article 725 Type CL3R
- NEC Article 800 Type CMR

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
DS92202	22	2	.008"	.015"	.122"	8.6
DS92203	22	3	.008"	.015"	.129"	11
DS92204	22	4	.008"	.015"	.141"	15.1
DS92206	22	6	.008"	.015"	.161"	20
DS92208	22	8	.008"	.015"	.180"	26.2
DS92210	22	10	.008"	.015"	.212"	36
DS92212	22	12	.008"	.015"	.219"	42
DS92002	20	2	.008"	.015"	.134"	11
DS92004	20	4	.008"	.015"	.156"	20

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

COLOR CODE CHART

Cond. #	Color
1	Black
2	Red
3	White
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow
9	Purple
10	Gray
11	Pink
12	Tan