

## Extra Flexible Conduit

### Description

- Non-UL Extra Flexible Steel Conduit
- High grade galvanized low carbon steel
- Interlocking design
- Corrosion resistant

### Applications

- Flexible metal raceway for specific applications where UL and other agency approvals are not required
- Motor leads
- Made in USA of US and/or imported materials

ORDERING INFORMATION						PRODUCT DIMENSIONS/BEND RADIUS		
Product Code	Trade Size (inches)	Trade Size (mm)	Coil Length (feet)	Reel Length (feet)	Approx. Weight/ 100 feet (pounds)	Internal Diameter (min/max) inches	External Diameter (min/max) inches	Bend Radius inches (mm)
5201-42-00	3/8	12	250'	—	8	0.375/0.393	0.560/0.610	2
5201-45-00	3/8	12	—	500'	8	0.375/0.393	0.560/0.610	2
5201-60-00	3/8	12	—	1000'	8	0.375/0.393	0.560/0.610	2
5203-30-00	1/2	16	100'	—	16	0.625/0.645	0.860/0.920	3
5203-45-00	1/2	16	—	500'	16	0.625/0.645	0.860/0.920	3
5203-60-00	1/2	16	—	1000'	16	0.625/0.645	0.860/0.920	3
5204-30-00	3/4	21	100'	—	21	0.812/0.835	1.045/1.105	4
5205-24-00	1	27	50'	—	34	1.000/1.040	1.300/1.380	5
5206-24-00	1-1/4	35	50'	—	42	1.250/1.300	1.550/1.630	6.25
5207-22-00	1-1/2	41	25'	—	63	1.500/1.575	1.850/1.950	7.50
5208-22-00	2	53	25'	—	84	2.000/2.080	2.350/2.450	10
5209-22-00	2-1/2	63	25'	—	104	2.500/—	2.860/3.060	12.5
5210-22-00	3	78	25'	—	125	3.000/—	3.360/3.560	15
5211-22-00	3-1/2	91	25'	—	145	3.500/—	3.860/4.060	17.5
5212-22-00	4	103	25'	—	165	4.000/—	4.360/4.560	20

NOTE: All dimensions and weights are subject to normal manufacturing tolerances.