

### APPLICATIONS

- HVAC equipment
- Machine tools
- Marine equipment
- Motors & controls
- Printing equipment
- Pumps
- Refrigeration equipment
- Transformer connections
- Outdoor lighting

### NEW PRODUCT SHOWCASE

## Exciting news for Kwikflex® NMLT!

- **UL LISTED IN ANY LENGTH**
- **NEW MULTI-ANGLE CONNECTOR**
- **EASY TO SHIP CARTONS**

**Kwikflex® NMLT**  
**Type B on reels are**  
**UL listed in all**  
**lengths**

Available in sizes from 3/8" to 2", reels offer the end user the best possible continuous length in the market place. Its patented design offers a low profile coupling that when two conduits are connected it is hardly noticeable and allows the user to run the conduit at any length desirable. There is no longer any need for additional parts when making a long conduit run.

Kwikflex NMLT is also available in extra-flexible formulations in sizes 3/8" to 2"

### Coils come packaged in easy to ship cartons

Coils are conveniently packaged in cardboard boxes to keep the pipe clean and come with a center knock-out for easy dispensing.

### NEW Multi Angle Connector

Kwikflex fittings are available in a full range of matching sizes in straight, 90 degree and in a **NEW** multi-angle configuration. The new Multi-Angle Conduit Connector features a unique swivel design which allows for:

- ❖ **Multiple angle installations**
- ❖ **45 degree installations**
- ❖ **The ultimate in flexibility for your job**



**KRALOY®**  
*The Fitting Choice*

Toll Free: (800) 265-1815

Direct: (519) 681-2140



[www.kraloyfittings.com](http://www.kraloyfittings.com)

Products are manufactured by IPEX Electrical Inc. and distributed in the United States by Kraloy, a division of Multi Fittings Corp.


Kraloy® is a trademark of Multi Fittings Corp.



Kwikflex® is a trademark of IPEX Branding Inc.

## NMLT CONDUIT

	Size inches	Product Code	Length feet
 	3/8	165005	100
	1/2	165007	100
	3/4	165009	100
	1	165011	100
	1-1/4	165014	100
	1-1/2	165017	50
	1-1/2	165021	100
	2	165020	50



### NMLT Flexible Conduit Reels (Grey) Type B

	1/2	165082	1000
	3/4	165085	700
	1	165090	500

	Size inches	Product Code	Length feet
 	3/8	165055	100
	1/2	165057	100
	3/4	165059	100
	1	165061	100
	1-1/4	165064	100
	1-1/2	165067	100
	2	165070	100

Other packages sizes available on request



## NMLT FITTINGS

	Size inches	Part Number	Product Code
 	3/8	LTB03/90	065306
	1/2	LTB10/90	065307
	3/4	LTB15/90	065310
	1	LTB20/90	065312
	1-1/4	LTB25/90	065314
	1-1/2	LTB30/90	065317
	2	LTB35/90	065320



### NMLT Straight Fittings (Grey)

 	3/8	LTS03	065326
	1/2	LTS10	065327
	3/4	LTS15	065330
	1	LTS20	065332
	1-1/4	LTS25	065334
	1-1/2	LTS30	065337
	2	LTS35	065340



### NMLT Screw-on 90° Elbows (Grey)

 	1/2	LTD10/90	065350
	3/4	LTD15/90	065352

### NMLT Screw-on Straight Fittings (Grey)

 	1/2	LTD10	065360
	3/4	LTD15	065362

### NMLT Screw-on Multi Angle Fittings (Grey)

 	1/2	LTMA10	065015
	3/4	LTMA15	065016