








ELECTRICAL ACCESSORIES

Household Devices

QUICK CLAMP PLUGS & CONNECTORS

	CATALOG NUMBER	RATING	DESCRIPTION	COLOR	UL	CSA
	123PQC	10A with 18AWG SPT-1 & 2 Cord, 13A with 16AWG SPT-1 Cord	2 wire Quick Clamp plug	Brown	•	
	123PQCW			White	•	
	123C3W		2 wire tri-tap Quick Clamp connector	White	•	

ADAPTERS

	125	15A 660W	125V	Lampholder to outlet, medium base.	White	•	
	1403	660W	125V	Medium base lampholder/outlet adapter, keyless lampholder with 2 outlets, 2 Pole, 2 Wire.	Black	•	
	1406	250W	125V	Medium base lampholder/outlet adapter, pull chain lampholder with 2 outlets, 2 Pole, 2 Wire.	Black	•	
	1406I				Ivory	•	
	128	15A 660W	250V	Single lampholder-to-twin lampholder, medium base.	Brown	•	
	8681	660W	250V	Mogul to medium socket adapter, 1 piece. 1.66" Dia. x 2.0" Deep	White	•	•
	313CC10	75W	125V	Socket reducer, medium to candelabra, keyless.	Black	•	•
	1264	15, 20A	125V	Travel trailer adapter, 2 Pole, 3 Wire.			
	210G	15A	125V	Adapter, parallel blades, molded rubber, polarized, 3 Wire grounding.	Gray	•	
	1482ICC10	15A	125V	Cube tap, single to triple outlet, 2 Pole, 3 Wire.	Ivory	•	•
	68	15A	125V	Cube tape, phenolic, single to triple, 2 Pole, 2 Wire.	Brown		
	68I				Ivory		
	63	15A	125V	Plug-in adapter, single to triple, polarized, 2 Pole, 2 Wire.	Brown	•	•
	63I				Ivory	•	•
	69I	15A	125V	Plug-in adapter, single to triple, swivel, polarized, 2 Pole, 2 Wire.	Ivory	•	•
	69W				White	•	•