



VICTOR "SNAP ON" STEEL STRAPS

FOR HEAVY WALL CONDUIT (RIGID)

CONDUIT SIZE (RIGID)	VICTOR PART NUMBER	PRICE LIST PAGE	MOUNTING HOLE SIZE	MATERIAL THICKNESS	MATERIAL WIDTH	PIECES PER BOX	PIECES PER CARTON	LBS PER CARTON
----------------------------	--------------------------	-----------------------	--------------------------	-----------------------	-------------------	----------------------	-------------------------	----------------------

STANDARD SERIES

1/8	10020-S	1	9/32	.062	5/8	100	1000	25
1/4	10021-S	1	9/32	.062	5/8	100	1000	27
3/8	10022-S	1	9/32	.062	5/8	100	1000	30
1/2	10023-S	1	9/32	.062	5/8	100	1000	35
3/4	10024-S	1	9/32	.062	5/8	50	500	21
1	10025-S	1	9/32	.062	5/8	50	500	22
1 1/4	10026-S	1	9/32	.062	5/8	50	250	15
1 1/2	10027-S	1	9/32	.062	5/8	50	250	17
2	10028-S	1	9/32	.062	5/8	-	100	8
2 1/2	10029-S	1	11/32	.093	3/4	-	50	9
3	10030-S	1	11/32	.093	3/4	-	50	11
3 1/2	10031-S	1	11/32	.093	3/4	-	50	11
4	10032-S	1	11/32	.093	3/4	-	50	11
5	10033-S	1	11/32	.093	3/4	-	20	7
6	10034-S	1	11/32	.093	3/4	-	20	8

SMALL HOLE SERIES

1/8	19220-S	4	7/32	.062	5/8	100	1000	25
1/4	19221-S	4	7/32	.062	5/8	100	1000	27
3/8	19222-S	4	7/32	.062	5/8	100	1000	30
1/2	19223-S	4	7/32	.062	5/8	100	1000	35
3/4	19224-S	4	7/32	.062	5/8	100	500	20
1	19225-S	4	7/32	.062	5/8	50	500	22
1 1/4	19226-S	4	7/32	.062	5/8	50	250	15

HEAVY SERIES

1/2	10723-S	2	9/32	.093	3/4	100	500	30
3/4	10724-S	2	9/32	.093	3/4	50	SC0	36
1	10725-S	2	9/32	.093	3/4	50	250	21
1 1/4	10726-S	2	13/32	.125	1	-	100	18
1 1/2	10727-S	2	13/32	.125	1	-	50	10
2	10728-S	2	13/32	.125	1	-	50	14
2 1/2	10729-S	2	13/32	.125	1	-	50	15
3	10730-S	2	13/32	.125	1	-	25	9
3 1/2	10731-S	2	13/32	.125	1	-	25	12
4	10732-S	2	13/32	.125	1	-	25	12
5	10733-S	2	13/32	.125	1	-	20	13
6	10734-S	2	13/32	.125	1	-	20	14

LIGHT WEIGHT SERIES

1/4	10621-S	1	7/32	.032	5/8	100	1000	14
3/8	10622-S	2	7/32	.032	5/8	100	1000	18
1/2	10623-S	2	7/32	.032	5/8	100	1000	21
3/4	10624-S	2	7/32	.032	3/4	100	500	14
1	10625-S	2	7/32	.032	3/4	50	500	17

FOR "BX" CABLE

14-2	10605-S	1	3/16	.032	1/2	100	1000	11
	19205-S	4	7/32	.062	5/8	100	1000	25