



White

Model	Width	Body Height	No. Lights	Max. Watt.
SL8410-8	6"	7½"	1	60w

- White glass globe
- Pull-chain switch



White

Model	Width	Body Height	No. Lights	Max. Watt.
SL8436-8	6"	7½"	1	60w

- White glass globe



Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL8436-78	6"	7½"	1	60w

- White glass globe



White

Model	Width	Body Height	No. Lights	Max. Watt.
SL325-8	7½"	4½"	1	60w
SL326-8	9½"	5½"	2	60w
SL328-8	11½"	5½"	3	60w

- Rated for 90° supply wire



White

Model	Width	Body Height	No. Lights	Max. Watt.
SL8439-8	7½"	4¾"	1	60w
SL8440-8	9½"	5⅝"	2	60w

- Clear ribbed glass



Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL8455-78	7½"	4½"	1	60w
SL8456-78	9½"	5½"	2	60w

- Swirl alabaster style glass



Tile Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
SL8455-8I	7½"	4½"	1	60w
SL8456-8I	9½"	5½"	2	60w

- Swirl alabaster style glass
- Rated for 90° supply wire



Polished Brass

Model	Width	Body Height	No. Lights	Max. Watt.
SL8651-I	11¼"	5½"	1	100w
SL8652-I	13¼"	5½"	2	60w
SL8653-I	15½"	5½"	3	60w

- Etched swirl glass
- Rated for 90° supply wire



Polished Brass

Model	Width	Body Height	No. Lights	Max. Watt.
SL8681-I	11¼"	5½"	1	100w
SL8682-I	13¼"	5½"	2	60w
SL8683-I	15½"	5½"	3	60w

- Etched melon glass
- Rated for 90° supply wire