



ED17

ED17
PROTECTED

ED28

BT28
PROTECTED

ED37



BT37

BT37
PROTECTED

BT56

METAL HALIDE LAMPS (FOR USE IN ENCLOSED FIXTURES)

Energy Used (Watts)	Base	Order No.	Footnotes	Domestic Code	Master Pack	Finish	Avg. Rated Hours	Brightness (Initial Lumens)	Brightness (Mean Lumens)	Light Appearance (Kelvin)	CRI	ANSI Code	Life in Years*	Est. Yearly Energy Cost**	MOL	MOD
ED17																
50	Medium	37016	1,3	MH50/U/M110/E/MED	6	Clear	10000	3400	2000	4200	65	M110/E	9.1	\$6.02	5 7/16"	2 1/4"
70	Medium	37017	1,3	MH70/U/M98/E/MED	6	Clear	10000	5600	4400	4200	65	M98/E	9.1	\$8.43	5 7/16"	2 1/4"
100	Medium	37018	1,3	MH100/U/M90/E/MED	6	Clear	10000	8500	5525	4200	65	M90/E	9.1	\$12.05	5 7/16"	2 1/4"
150	Medium	37015	1,3	MH150/U/M102/E/MED	6	Clear	10000	9000	8000	4200	60	M102/E	9.1	\$18.07	5 7/16"	2 1/4"
175	Medium	37019		MH175/U/M57/E/MED	6	Clear	10000	14400	11520	4200	65	M57/E	9.1	\$21.08	5 7/16"	2 1/4"
ED28																
175	Mogul	37020	3	MH175/U/M57/E	6	Clear	10000	14400	12800	4200	65	M57/E	9.1	\$21.08	8 5/16"	3 5/8"
250	Mogul	37021	3	MH250/U/M58/E	6	Clear	10000	20500	17500	4200	65	M58/E	9.1	\$30.11	8 5/16"	3 5/8"
400	Mogul	37014	2,3	MH400/U/M59/ED28/E	6	Clear	20000	36000	23500	4000	60	M59/E	18.3	\$48.18	8 5/16"	3 5/8"
ED37																
400	Mogul	37024	3	MH400/U/M59/E	6	Clear	20000	36000	23500	4200	65	M59/E	18.3	\$48.18	11 1/2"	4 3/4"
BT37																
1000	Mogul	37028	2,3	MH1000/U/M47/E/BT37	6	Clear	10000	110000	86000	4200	65	M47/E	9.1	\$120.45	11 1/2"	4 3/4"
BT56																
1000	Mogul	37027	3	MH1000/U/M47/E	6	Clear	10000	105000	80000	4200	65	M47/E	9.1	\$120.45	15 1/2"	7 7/8"

METAL HALIDE PROTECTED LAMPS (OPEN FIXTURE RATED)

Energy Used (Watts)	Base	Order No.	Footnotes	Domestic Code	Master Pack	Finish	Avg. Rated Hours	Brightness (Initial Lumens)	Brightness (Mean Lumens)	Light Appearance (Kelvin)	CRI	ANSI Code	Life in Years*	Est. Yearly Energy Cost**	MOL	MOD
ED17																
50	Medium	37009	1,3	MP50/U/M110/O/MED	6	Clear	10000	3450	1900	3000	60	M110/O	9.1	\$6.02	5 7/16"	2 1/4"
70	Medium	37010	1,3	MP70/U/M98/O/MED	6	Clear	10000	5600	4480	3000	60	M98/O	9.1	\$8.43	5 7/16"	2 1/4"
100	Medium	37011	1,3	MP100/U/M90/O/MED	6	Clear	10000	8000	5525	3000	60	M90/O	9.1	\$12.05	5 7/16"	2 1/4"
150	Medium	37013	1,3	MP150/U/M102/O/MED	6	Clear	10000	12250	8500	4200	60	M102/O	9.1	\$18.07	5 7/16"	2 1/4"
BT28																
175	Ext. Mogul	37029	3	MP175/U/M57/O	6	Clear	10000	14400	10800	4200	65	M57/O	9.1	\$21.08	8 1/4"	3 5/8"
250	Ext. Mogul	37023		MP250/BU/M58/O	6	Clear	10000	20500	17500	4200	65	M58/O	9.1	\$30.11	8 1/4"	3 5/8"
BT37																
400	Ext. Mogul	37022		MP400/BU/M59/O	12	Clear	20000	36000	23500	4200	65	M59/O	18.3	\$48.18	11 1/2"	4 3/4"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh — Cost depends on rates and use.

Contains mercury. (Hg) For more on clean up and safe disposal, visit epa.gov/cfl.

Footnotes

- 1 For Probe Start or Pulse Start Ballasts
- 2 Low Profile

3 Universal Operating Position