



FEATURES & SPECIFICATIONS

PRODUCT OVERVIEW

Arm-mounted security light for yards and lots, service roads and building perimeters. **Certain airborne contaminants can diminish integrity of acrylic.**

[Click here for Acrylic Environmental Compatibility table for suitable uses.](#)

CONSTRUCTION

Rugged, die-cast aluminum head.

Formed aluminum reflector and open-bottom refractor for ease of maintenance and lamp replacement. Prismatic refractor provides uniform symmetrical Type V distribution. Mounting arm and all mounting hardware included in carton. Photocell and lamp are included. 120V.

LISTINGS

Listed and labeled to UL standards for wet locations.

Listed and labeled to CSA standards.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select


Security Lights




TDD



TDD65



TDD



TDD65

ORDERING INFORMATION

Catalog Number	UPC	Description	Wattage	Lamp Source	Voltage	Mounting Arm Length	Lamp Included	Approx. Weight (lbs)	Pallet Qty	Standard Carton Qty
TDD100ML 120 M2	745974100140	12" security light	100	MH	120	24"	Y	12	24	2
TDD150SL 120 M2	745973506172	12" security light	150	HPS	120	24"	Y	12	24	2
TDD65L 120 M2	745974487494	10" security light	65	Fluorescent	120	18"	Y	4	32	2

Accessories: Order as separate catalog number.

CF65QT41 M6	Replacement for 65W fluorescent lamp.
RK1 TDDLENS M6	Reflector/lens assembly for HID only.