





























## HBLALU3800 Series

<b>HBLALU3800 Series</b>	<b>Description</b> <b>Single Channel Base</b> Satin anodized finish. Packed 40 ft. (12.19m) per carton, 10 ft. (3m) lengths.  Assembled cover and base dimensions. W: 3.00" (76.20) H: 2.25" (57.15)	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3800B10</b> A: 2.10" (53.34) B: 3.00" (76.20)	<b>Description</b> <b>Cover</b> Satin anodized finish. Packed 40 ft. (12.19m) per carton, 5 ft. (1.5m) lengths.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALUC5</b> A: 3.00" (76.20)
	 			 		
<b>Elbows and Tees</b>	<b>Description</b> <b>Internal Elbow</b> For making a 90° internal turn in a raceway run.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3817*</b> A: 6.00" (152.40) B: 6.00" (152.40)	<b>Description</b> <b>Inverted Internal Elbow</b> For connecting a vertical run of HBLALU3800 with a horizontal run with its cover facing up.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3817N*</b> A: 6.00" (152.40) B: 5.98" (151.89)
	 			 		
	<b>Description</b> <b>External Elbow</b> For making a 90° external turn in a raceway run.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3818*</b> A: 6.00" (152.40) B: 6.00" (152.40)	<b>Description</b> <b>Tee</b> For branch connections of two runs of HBLALU3800 Raceway.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3815*</b> A: 6.00" (152.40) B: 6.00" (152.40)
	 			 		
<b>End Fittings</b>	<b>Description</b> <b>Flat Elbow</b> For making a 90° flat turn in a raceway run.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3811*</b> A: 6.00" (152.40) B: 6.00" (152.40)	<b>Description</b> <b>Blank End Fitting</b> For closing end of raceway.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3810B</b> A: 3.00" (76.20) B: 2.31" (58.74)
	 			 		
<b>Fittings</b>	<b>Description</b> <b>Entrance End Fitting</b> For feeding raceway, has concentric ½ in. and ¾ in. trade size KOs.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU3810B1</b> A: 3.00" (76.20) B: 2.31" (58.74)	<b>Description</b> <b>Cover Clip</b> To cover seam where lengths of HBLALU3800 Raceway come together.	<b>Color</b> Stainless Steel	<b>Catalog Number</b> <b>HBLALU3806</b> A: 1.38" (34.92)
	 			 		
	<b>Description</b> <b>Wire Clip</b> For holding conductors in place. Can be used for either HBLALU3800 or HBLALU4800 Raceway.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALUWC</b> A: 1.00" (25.40)	<b>Description</b> <b>Internal Corner Coupling</b> For butting two raceway sections to form an internal 90° turn in a raceway run.	<b>Color</b> Anodized Aluminum	<b>Catalog Number</b> <b>HBLALU17A</b> A: 4.00" (101.80) B: 2.00" (50.83)
	 			 		
	<b>Description</b> <b>Couplings (Pair)</b> To join lengths of HBLALU3800 or HBLALU4800 base.	<b>Color</b> Aluminum	<b>Catalog Number</b> <b>HBLALU01</b> A: 2.85" (72.39) B: 4.00" (101.80)	<b>Description</b> <b>Grounding Adapter</b> For connection of equipment grounding. #10-32 Locking screws included.	<b>Color</b> Galvanized Steel	<b>Catalog Number</b> <b>HBLALU09</b> A: 4.00" (101.80) B: 2.00" (50.83)
	 			 		

Note: \*HBLALU01 couplings included.  
See page T-40 for cover plates.

Dimensions in Inches (mm)