

Dimmable LED Deco Lamps

LED DIMMABLE DECO LAMPS, 5W



LED5E26S1430K




LED5E12B1127K
LED4E12B1127K




LED5E26B1127K
LED4E26B1127K




LED5E12B1127KF
LED4E12B1127KF



LED5E26B1127KF
LED4E26B1127KF



LED5E12G1627K
LED4E12G1627K




LED5E12G1627KF
LED4E12G1627KF




LED5E12F1127K
LED4E12F1127K



LED5E26G1627K
LED4E26G1627K



LED5E12G1627KF
LED4E12G1627KF




LED5E26F1127K
LED4E26F1127K




LED5E12F1127KF
LED4E12F1127KF




LED5E26F1127KF
LED4E26F1127KF



LED5E12F1127K
LED4E12F1127K



LED5E12F1127KF
LED4E12F1127KF



LED5E26F1127K
LED4E26F1127K

Item Number	ENERGY STAR®	Item Description	Voltage	Lamp Watts	Incandescent Comparison (Watts)	Lumens	LPW	CCT	CRI	STK/MTD	Case Quantity
LED5E26S1427K		LED 5W WET LOCATION S14 - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26S1430K		LED 5W WET LOCATION S14 - 3000K	120	5	40W	300	60.0	3000K	82	STK	12
LED5E26S1441K		LED 5W WET LOCATION S14 - 4100K	120	5	40W	300	60.0	4100K	82	STK	12
LED5E26S1427KF		LED 5W WET LOCATION S14 - 2700K Frosted	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26S1430KF		LED 5W WET LOCATION S14 - 3000K Frosted	120	5	40W	300	60.0	3000K	82	STK	12
LED5E26S1441KF		LED 5W WET LOCATION S14 - 4100K Frosted	120	5	40W	300	60.0	4100K	82	STK	12
LED5E26S14RD		LED 5W WET LOCATION S14 - RED	120	5	40W	300	60.0	—	82	STK	12
LED5E26S14GR		LED 5W WET LOCATION S14 - GREEN	120	5	40W	300	60.0	—	82	STK	12
LED5E12B1127K	★	LED 5W DIM CANDELABRA BLUNT 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26B1127K	★	LED 5W DIM BLUNT TIP - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E12B1127KF		LED 5W DIM CANDELABRA FROST BLUNT - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26B1127KF		LED 5W DIM FROST BLUNT TIP - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E12G1627K		LED 5W DIM CANDELABRA G16 GLOBE - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26G1627K		LED 5W DIM G16 GLOBE - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E12G1627KF		LED 5W DIM CANDELABRA FROST G16 GLOBE - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26G1627KF		LED 5W DIM FROST G16 GLOBE - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E12F1127K		LED 5W DIM CANDELABRA F11 Flame Tip - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26F1127K		LED 5W DIM F11 Flame Tip - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E12F1127KF		LED 5W DIM CANDELABRA FROST F11 Flame - 2700K	120	5	40W	300	60.0	2700K	82	STK	12
LED5E26F1127KF		LED 5W DIM FROST F11 Flame Tip - 2700K	120	5	40W	300	60.0	2700K	82	STK	12

LED DIMMABLE DECO LAMPS, 4W

LED4E12B1127K		LED 4W DIM CANDELABRA BLUNT TIP - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26B1127K		LED 4W DIM BLUNT TIP - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E12B1127KF	★	LED 4W DIM CANDELABRA FROST BLUNT - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26B1127KF	★	LED 4W DIM FROST BLUNT TIP - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E12G1627K	★	LED 4W DIM CANDELABRA G16 GLOBE - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26G1627K	★	LED 4W DIM G16 GLOBE - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E12G1627KF	★	LED 4W DIM CANDELABRA FROST G16 GLOBE - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26G1627KF	★	LED 4W DIM FROST G16 GLOBE - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E12F1127K		LED 4W DIM CANDELABRA F11 Flame - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26F1127K		LED 4W DIM F11 Flame Tip - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E12F1127KF		LED 4W DIM CANDELABRA FROST F11 Flame - 2700K	120	4	25W	200	50.0	2700K	82	STK	12
LED4E26F1127KF		LED 4W DIM FROST F11 Flame Tip - 2700K	120	4	25W	200	50.0	2700K	82	STK	12

★ ENERGY STAR® Rated (at time of print)



5 YEAR WARRANTY

*Based on 12 Hours per day