

AMERICANA

A timeless collection with subtle, elegant details. The delicate cast scroll arms enhance any ambience. Features decorative center columns and traditional candle lights.

FIVE-LIGHT CHANDELIER

P4346-09 Brushed Nickel
P4346-10 Polished Brass
P4346-20 Antique Bronze
24" dia., 17" ht.
Overall ht. w/chain 53"; wire 15'.
Five candelabra base lamps,
each 60w max.

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Antique Bronze - 20

*Optional fabric shades
P8639-01*



*See our catalog for
these and other shade
options for Americana*

SEMI-FLUSH CONVERTIBLE

P4354-09 Brushed Nickel
P4354-20 Antique Bronze
Hanging and ceiling mount
hardware included.
13" dia., 12-7/8" ht.
Overall ht. w/chain 53", wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P4355-09 Brushed Nickel
P4355-10 Polished Brass
P4355-20 Antique Bronze
23-1/4" dia., 18-1/4" ht.
Overall ht. w/chain 58"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P4356-09 Brushed Nickel
P4356-10 Polished Brass
P4356-20 Antique Bronze
23-1/4" dia., 18" ht.
Overall ht. w/chain 57"; wire 15'.
Six candelabra base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P4357-09 Brushed Nickel
P4357-10 Polished Brass
P4357-20 Antique Bronze
26" dia., 18" ht.
Overall ht. w/chain 54"; wire 15'.
Eight candelabra base lamps,
each 60w max.

TEN-LIGHT CHANDELIER

P4358-09 Brushed Nickel
P4358-20 Antique Bronze
Two-tier.
26" dia., 23" ht.
Overall ht. w/chain 67"; wire 15'.
Ten candelabra base lamps,
each 60w max.



P4354-09



P4354-20



P4346-09



P4346-10



P4346-20



P4355-09



P4355-10



P4355-20



P4356-09



P4356-10



P4356-20



P4357-09



P4357-10



P4357-20



P4358-09



P4358-20