


FEATURES & BENEFITS


- Polycarbonate lexan spring loaded cover
- ♦ 12 top holes w/polycarbonate lexan bushings
- Reinforced hand hold cover
- Anchor bolts and template included
- Easily secured base cover
- Bronze polyester powder-coat finish
- Pole cap is included
- Conforms to ASTM-A-500 Grade B; Minimum yield strength of 46,000 PSI
- Polyester powder coated finish on Sandblasted Surface Chemical Treated to insure Maximum Paint Adhesion, Baked at 400° to ensure Maximum Hardness and Durability
- ♦ Wall Thickness available in Gauge 11 (.120°) or Gauge 7 (.180")
- ♦ Meets ASTM 500 standard


Item Number	Dimensions (LxWxH)
MIPK164SQNT	16 ft. 4x4 Square 11 Gauge Pole
MIPK204SQNT	20 ft. 4x4 Square 11 Gauge Pole
MIPK254SQNT	25 ft. 4x4 Square 11 Gauge Pole

Shaft Size	Gauge	Base Plate Size	Bolt Circle	Bolt Size	Weight (lbs)
16'	11	10.5" x 10.5" x 3/4"	9" - 3/16"	3/4" x 30"	135
20'	11	10.5" x 10.5" x 3/4"	9" - 3/16"	3/4" x 30"	146
25'	11	10.5" x 10.5" x 3/4"	12" - 3/4"	1" x 36"	256









Wind Specifications

POLE	80 MPH Max EPA	80 MPH Max Fixture Weight (lbs)	90 MPH Max EPA	90 MPH Max Fixture Weight (lbs)	100 MPH Max EPA	100 MPH Max Fixture Weight (lbs)
16' 4SQ 11 Ga.	10.1	300	7.6	264	5.0	260
20' 4SQ 11 Ga.	10.1	320	7.6	279	5.0	275
25' 4SQ 11 Ga.	6.2	250	3.8	225	2.0	200


Dimensions and specifications subject to change without notice.



CAT#

JOB NAME

TYPE







ACCESSORIES



Item #	Description	Finish/Color	Weight (lbs)	Units/Carton
MITVA4	4" Square Vertical Tenon	Bronze	2.7	12
MITVA5	5" Square Vertical Tenon	Bronze	2.9	12



Item #	Description	Finish/Color	Dimensions	Weight (lbs)	Units/Carton
MITV2	Twin Square Vertical Tenon	Bronze	24 2/5"	4.2	1



I	Item #	Description	Finish/Color	Dimensions	Weight (lbs)	Units/Carton
	MITV3	Triple Square Vertical Tenon	Bronze	24 2/5"x24 2/5"	4.2	1

2" Slip Fitter



Item #	Description	Finish/Color	Dimensions	Weight (lbs)	Units/Carton
MITVC4	90° Quad Square Vertical Tenon	Bronze	34 1/4"	4.9	1

2" Slip Fitter



Item #	Description	Finish/Color	Dimensions	Weight (lbs)	Units/Carton
MITV4	180° Quad Square Vertical Tenon	Bronze	24"x24"x24"	5.7	1

2 Piece U-bracket



Adjustable Slip Fitter

Mounting Arm 6"



Mounting Arm 10"

Accessories

MIA41

MI2AF

MISSA-M

MISSA

Dimensions and specifications subject to change without notice.

♦ 800-444-WATT → www.mobern.com →
 8200 Stayton Dr., Ste. 500, Jessup, MD 20794

CAT#	

JOB NAME

TYPE