



Buchanan Multi-Purpose Cable Ties



Features

- General purpose cable tie for every day bundling and cable management
- UL recognized

Models Specifications

Size	Thickness & Width	Color	Tensile Strength (lbs.)	Pkg. Qty.	Cat. No.
Miniature Ties					
4"	.039 x .095	Natural	18	100	B-4-18-9-C
4"	.039 x .095	Natural	18	1000	B-4-18-9-M
4"	.039 x .095	UV Black	18	100	B-4-18-0-C
Intermediate Ties					
6"	.047 x .142	Natural	40	100	B-6-40-9-C
6"	.047 x .142	Natural	40	1000	B-6-40-9-M
6"	.047 x .142	UV Black	40	100	B-6-40-0-C
Standard Air Handling Ties					
8"	.053 x .178	Burgandy	50	100	B-8-50-35-C
11"	.053 x .178	Burgandy	50	100	B-11-50-35-C
Standard Ties					
8"	.057 x .181	Natural	50	100	B-8-50-9-C
8"	.057 x .181	Natural	50	500	B-8-50-9-D
8"	.057 x .181	Natural	50	1000	B-8-50-9-M
8"	.057 x .181	UV Black	50	100	B-8-50-0-C

8"	.057 x .181	UV Black	50	1000	B-8-50-0-M
11"	.057 x .181	Natural	50	100	B-11-50-9-C
11"	.057 x .181	Natural	50	500	B-11-50-9-D
11"	.057 x .181	UV Black	50	100	B-11-50-0-C
11"	.057 x .181	UV Black	50	500	B-11-50-0-D
14"	.057 x .181	Natural	50	100	B-14-50-9-C
14"	.057 x .181	Natural	50	500	B-14-50-9-D
14"	.057 x .181	UV Black	50	100	B-14-50-0-C
14"	.057 x .181	UV Black	50	500	B-14-50-0-D
Heavy-Duty Ties					
14"	.066 x .299	Natural	120	50	B-14-120-9-C
14"	.066 x .299	UV Black	120	50	B-14-120-0-L
24"	.066 x .299	Natural	175	50	B-24-175-9-L
24"	.066 x .299	UV Black	175	50	B-24-175-0-L
36"	.066 x .299	UV Black	175	50	B-36-175-0-L
36"	.066 x .299	Natural	175	50	B-36-175-9-L
48"	.066 x .299	Natural	175	50	B-48-175-9-L
48"	.066 x .299	UV Black	175	50	B-48-175-0-L
Mounting Ties					
8"	.057 x .189	Natural	50	100	B-8-50MT-9-C
8"	.057 x .189	UV Black	50	100	B-8-50MT-0-C
14"	.053 x .178	Natural	50	100	B-14-50MT-9-C
14"	.053 x .178	UV Black	50	100	B-14-50MT-0-C
Mounting Pads					
3/4" x 3/4"	.142 Max. Tie Width	Natural	N/A	100	BMP-750-9-C
1" x 1"	.189 Max. Tie Width	Natural	N/A	100	BMP-1000-9-C