



PAR38

PAR30

PAR30SN

PAR20

## PAR38, PAR30 & PAR20

### Features & Benefits

- Energy efficient: up to 85% less energy than standard halogen replacement.
- Smooth, uniform dimming.
- Unique full face optic that provides designer grade light quality with same look as halogen replacement.
- Smooth, clean outside housing seamlessly blends into lighting applications.



### Dimmable Designer Elite LED PAR Lamps

Item Number

ENERGY STAR®  
Item Description

Voltage

Lamp Watts

Lumens

Lumens Per Watt

\*CBCP

Beam Angle

CCT

CRI

STK/MTD

Case Quantity

#### 17W ELITE DESIGNER DIMMABLE PAR38 (REPLACES 120W)



LED17P38D24KFL	17W Smooth PAR38 - 2400K 40 Degree	120	17	1200	70.6	2231	40	2400K	82	MTD	12
LED17P38D24KNFL	17W Smooth PAR38 - 2400K 25 Degree	120	17	1200	70.6	5382	25	2400K	82	MTD	12
LED17P38D24KSP	17W Smooth PAR38 - 2400K 15 Degree	120	17	1200	70.6	12059	15	2400K	82	MTD	12
LED17P38D27KFL	17W Smooth PAR38 - 2700K 40 Degree	120	17	1200	70.6	2231	40	2700K	82	STK	12
LED17P38D27KNFL	★ 17W Smooth PAR38 - 2700K 25 Degree	120	17	1200	70.6	5382	25	2700K	82	STK	12
LED17P38D27KSP	17W Smooth PAR38 - 2700K 15 Degree	120	17	1200	70.6	12059	15	2700K	82	MTD	12
LED17P38D30KFL	★ 17W Smooth PAR38 - 3000K 40 Degree	120	17	1250	73.5	2231	40	3000K	82	STK	12
LED17P38D30KNFL	★ 17W Smooth PAR38 - 3000K 25 Degree	120	17	1250	73.5	5382	25	3000K	82	STK	12
LED17P38D30KSP	17W Smooth PAR38 - 3000K 15 Degree	120	17	1250	73.5	12059	15	3000K	82	MTD	12
LED17P38D35KFL	17W Smooth PAR38 - 3500K 40 Degree	120	17	1275	75.0	2231	40	3500K	82	MTD	12
LED17P38D35KNFL	17W Smooth PAR38 - 3500K 25 Degree	120	17	1275	75.0	5382	25	3500K	82	MTD	12
LED17P38D35KSP	17W Smooth PAR38 - 3500K 15 Degree	120	17	1275	75.0	12059	15	3500K	82	MTD	12
LED17P38D41KFL	17W Smooth PAR38 - 4100K 40 Degree	120	17	1300	76.5	2231	40	4100K	82	MTD	12
LED17P38D41KNFL	17W Smooth PAR38 - 4100K 25 Degree	120	17	1300	76.5	5382	25	4100K	82	MTD	12
LED17P38D41KSP	17W Smooth PAR38 - 4100K 15 Degree	120	17	1300	76.5	12059	15	4100K	82	MTD	12
LED17P38D50KFL	17W Smooth PAR38 - 5000K 40 Degree	120	17	1300	76.5	2231	40	5000K	82	MTD	12
LED17P38D50KNFL	17W Smooth PAR38 - 5000K 25 Degree	120	17	1300	76.5	5382	25	5000K	82	MTD	12
LED17P38D50KSP	17W Smooth PAR38 - 5000K 15 Degree	120	17	1300	76.5	12059	15	5000K	82	MTD	12

★ ENERGY STAR® Rated (at time of print)



5 YEAR WARRANTY

\*Minimum CBCP est. Consult [tcp.com](http://tcp.com) for most current photometry and LM79 data.