

# BROOKSIDE

Inspired by vintage light fixtures found in early 20th century train stations. Metal shade and double prismatic glass options. LED options are 3000K, 90+ CRI.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

## MINI-PENDANT

**P5023-09** Brushed Nickel  
8" dia., 7-1/2" ht.  
Overall ht. w/stem 64"; wire 15'.  
One medium base lamp,  
100w max.

## PENDANT

**P5024-09** Brushed Nickel  
12" dia., 9-1/8" ht.  
Overall ht. w/stem 65"; wire 15'.  
One medium base lamp,  
150w max.

## LED PENDANT

**P5024-0930K9** Brushed Nickel  
**P5024-2030K9** Antique Bronze  
12" dia., 9-1/8" ht.  
Overall ht. w/stem 65"; wire 15'.  
One 17w LED module included.



PROGRESS **LED**



P5023-09



P5024-09  
P5024-0930K9



P5024-2030K9

# BROOKSIDE



Get inspired from vintage undertones and train station styling with this outdoor lantern collection. Available in aluminum with Gilded Iron finish or solid brass Antique Nickel or solid Copper that ages to a patina finish. Dark Sky compliant.

## FINISHES

- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

## SMALL WALL LANTERN

**P5721-14** Copper

**P5721-71** Gilded Iron

**P5721-81** Antique Nickel

8" W., 9-3/4" ht.

Extends 9-3/4". H/CTR 5-3/4".

One medium base lamp,  
60w max.

## MEDIUM WALL LANTERN

**P5722-14** Copper

**P5722-71** Gilded Iron

**P5722-81** Antique Nickel

10" W., 10-3/4" ht.

Extends 11-3/4". H/CTR 6-1/2".

One medium base lamp,  
75w max.

## LARGE WALL LANTERN

**P5723-14** Copper

**P5723-71** Gilded Iron

**P5723-81** Antique Nickel

12" W., 12-3/8" ht.

Extends 13-1/8". H/CTR 6-7/8".

One medium base lamp,  
100w max.



P5721-81



P5721-14



P5722-81



P5722-14



P5723-81



P5723-14



P5721-71



P5722-71



P5723-71

# BROOKSIDE LED

## FINISHES

- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

## LARGE WALL LANTERN

**P5723-1430K9** Copper

**P5723-7130K9** Gilded Iron

**P5723-8130K9** Antique Nickel

12" W., 12-1/4" ht.

Extends 13-1/4". H/CTR 6-7/8".

One 17w LED module included.



P5723-1430K9



P5723-7130K9



P5723-8130K9

## LED FEATURES

- 120v AC, replaceable module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**

*Shown: P5723-81 lanterns*

