safety products Z




GFCI Panel Mounts





32360-001 TI WHI





GFCI Panel Mounts

Provides GFCI protection for personnel and equipment when leakage levels have a potentially lethal ground current in excess of 6 milliamperes. Ideal for equipment where mounting applications require panel or bulkhead mount. Applications include:

- Control Panels
- Test Beds
- Pumping Systems
- Appliances

Automatic reset on power restoration following disruption of primary power. 41240-001 is manual reset.

FEATURES

32360 001-3

- Volts/Amps: 120V/20A
- L & N 12 AWG
- Trip Level: 4 6 mA



33120 001-3

- Volts/Amps: 120V/20A
- L & N 12 AWG
- ► Trip Level: 4 6 mA

41240 001-3

- Volts/Amps: 120V/20A
- Trip Level: 4 6 mA
- Manual Reset



33240 001-3

- Volts/Amps: 240V/20A
- L & N 12 AWG
- Trip Level: 4 6 mA



TECHNICAL DATA	
Grounded Neutral (33120 only)	4 Ohms typical
Trip response time for ground fault	less than 25mS
and grounded neutral trip	
Voltage surge withstand	3kv ringwave test and
	4kv/2kA surge immunity test
Radio frequency noise susceptibility	operates within normal limits with 0.5 volts
	injected on power line 150kHz-230mHz
Frequency	50 / 60 Hz
Endurance	3,000 operations minimum
Overload Current	six times rated current
Operating temperature range	-35°C to 66°C
Effect of 10 Amp turn DC Shock	5% maximum trip level variation
on ground fault trip	
Insulation voltage	1500 VRMS - 1 Min.
Power On indication	lighted indicator

