

TASKWORK DIRECT WIRE – 12V XENON

TaskWork Direct Wire 12V Xenon offers you a simple installation solution for illuminating a task area or adding ambient lighting.



10584 BZ
30" Fixture shown in Bronze

Select Appropriate Light Fixture Size & Finish

- 10579 BZ, SS, WH** 7"
- 7" L x 5" W x 1" H
 - 1 light
 - 12V, 18 Watt Xenon bulb included

- 10580 BZ, SS, WH** 12-1/4"
- 12-1/4" L x 5" W x 1" H
 - 2 light
 - 12V, 18 Watt Xenon bulbs included


- 10581 BZ, SS, WH** 21-1/2"
- 21-1/2" L x 5" W x 1" H
 - 3 light
 - 12V, 18 Watt Xenon bulbs included

- 10584 BZ, SS, WH** 30"
- 30" L x 5" W x 1" H
 - 4 light
 - 12V, 18 Watt Xenon bulbs included

- 10595 BZ, SS, WH** 40"
- 40" L x 5" W x 1" H
 - 5 light
 - 12V, 18 Watt Xenon bulbs included

Replacement Bulb
10574 CLR
■ 12V, 18 Watt Xenon, clear

Accessories



10588 SI - Duplex BX cable connector



10589 SI - Connector for NM & BX cable

AVAILABLE FINISHES


Bronze (BRZ), Brushed Stainless Steel (SS) and White (WH)



BZ Bronze




SS Brushed
Stainless Steel



WH White

BACK MOUNT DESIGN




FEATURES

- Low 1" profile x 5" wide
- Fastener-free hinge assembly
- Keyhole mounting
- NM & BX single cable connector included
- High/Low/On-Off switch

PERFORMANCE DATA (10580)

Lumens/Watt	6.1
Light Output FC	
A – Counter Front	14.1
B – Counter Middle	31.2
C – Counter Back	47.3
D – Counter Wall	17.8
CRI (color rendering)	min 100
CCT (color temperature)	2700K
Light Source Life	10,000 hrs.



TASKWORK DIRECT WIRE – 120V XENON

TaskWork Direct Wire 120V Xenon design features large wiring compartments and multiple 1/2" trade-size knockouts for fast and easy installation.



12013 BZ
22" Fixture shown in Bronze

Select Appropriate Light Fixture Size & Finish

12011 BZ, SI, WH

7"

- 7" L x 5" W x 1-1/4" H
- 1 light
- 120V, 20 Watt Xenon bulb included

12012 BZ, SI, WH

12"

- 12" L x 5" W x 1-1/4" H
- 2 light
- 120V, 20 Watt Xenon bulbs included

12013 BZ, SI, WH

21"

- 21" L x 5" W x 1-1/4" H
- 3 light
- 120V, 20 Watt Xenon bulbs included

12014 BZ, SI, WH

30"


- 30" L x 5" W x 1-1/4" H
- 4 light
- 120V, 20 Watt Xenon bulbs included

Replacement Bulb

12090 CLR

- 120V, 20 Watt Xenon, clear

Accessories




10588 SI - Duplex BX cable connector



10589 SI - Connector for NM & BX cable

BACK MOUNT DESIGN




FEATURES

- 1-1/4" profile x 5" wide
- 120V, 20 Watt Xenon bulb(s)
- High/Low/On-Off switch
- cUL Listed


PERFORMANCE DATA (12012)

Lumens/Watt	5
Light Output FC	
A – Counter Front	8.6
B – Counter Middle	21.1
C – Counter Back	38.2
D – Counter Wall	13.2
CRI (color rendering)	min 100
CCT (color temperature)	2620K
Light Source Life	2,500 hrs.




AVAILABLE FINISHES

Bronze (BRZ), Silver (SI) and White (WH)



BZ Bronze



SI Silver



WH White