




GFCIs PlugTail™ Specification Grade 15 & 20A, 125VAC


Ordering Information

Additional Features & Benefits	Catalog Number	Rating A. VAC	Color	NEMA Config. No.
PlugTail™ GFCI Receptacles				
 <p>Patented SafeLock™ Protection is standard on all P&S Specification Grade GFCIs.</p>	PT1595-*	15 125	I, W, Brown, GRY, BK, RED, LA	5-15R
	PT2095-*	20 125	I, W, Brown, GRY, BK, RED, LA	5-20R
PlugTail™ Combination Nightlight/GFCI Receptacles				
 <p>High impact-resistant lens made of Lexan®.</p> <p>Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.</p> <p>Photocell turns nightlight ON in dark, OFF in daylight.</p>	PT1595-NTL*	15 125	I, W, GRY, BK, RED, LA	5-15R
	PT2095-NTL*	20 125	I, W, GRY, BK, RED, LA	5-20R
PlugTail™ Tamper-Resistant GFCI Receptacles				
 <p>Dual mechanical shutter system to help prevent insertion of foreign objects.</p> <p>Patented UL Listed shutter system.</p>	PT1595-TR*	15 125	I, W, Brown, GRY, BK, RED, LA	5-15R
	PT2095-TR*	20 125	I, W, Brown, GRY, BK, RED, LA	5-20R

Catalog Number	Wire Type	Wire Length
PlugTail Connectors — Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

***Color Designation**

I	Ivory	GRY	Gray	RED	Red
W	White	BK	Black	LA	Light Almond
-	Brown				



GFCI - Specific Additional Features & Benefits:

Fits all electrical box and raceway applications. Right angle (90°) connector creates an easy mounting application.

Supplied with TP26 Decorator nylon wall plate.

For more information on these and other P&S products refer to our Catalog or visit our web site.