



Introducing the Metalux AP series, SLSHP – LED Shoplight series. The chain suspended SLSHP Fixture comes fully assembled with 5 ft. plug in cord and is ideal for portable and task lighting applications. This fully integrated LED fixture requires no lamps to install or replace with LEDs rated at 50,000 hours and a five year comprehensive warranty. Equivalent light output of two 4ft. Fluorescent Lamps with the efficiency of LED.

## Construction and Performance

- Fully assembled with 120V 5 ft. power cord for plug and play installation
- Two unique lumen packages - 3800 and 4800
- 4000K color temperature, excellent for task applications
- Fully frost lens for even illumination
- Easy on/off pull chain
- Includes 36" hanging chain and S hooks for easy mounting



## Reliability and Compliance

- LED's rated at 50,000 hrs.
- Five Year comprehensive warranty
- cULus listed for dry locations

MODEL#	PRODUCT DESCRIPTION	LED		COMPARED TO T12 FLUORESCENT		COMPARED TO T8 FLUORESCENT	
		LUMENS	WATTAGE	FIXTURE WATTAGE	ENERGY SAVINGS	FIXTURE WATTAGE	ENERGY SAVINGS
40SLSHP3840ND-120V	Utility LED Shoplight, 120V	3800	47W	62W	32%	56W	19%
40SLSHP4840ND-120V	High Output LED Shoplight, 120V	4800	63W	75W	19%	74W	17%

MODEL#	PRODUCT DESCRIPTION	UPC	UNIT CARTON	ENERGY QUALIFICATION
40SLSHP3840ND-120V	Utility LED Shoplight, 120V	080083706563	41.7 in. w x 4.8 in. h x 4.2 in. d	ENERGY STAR®
40SLSHP4840ND-120V	High Output LED Shoplight, 120V	080083713479	41.7 in. w x 4.8 in. h x 4.2 in. d	ENERGY STAR®

**Cooper Lighting**  
by **EATON**

Eaton's Cooper Lighting Business  
1121 Highway 74 South, Peachtree City, GA 30269

© 2015 Eaton. All Rights Reserved. Publication No. R15-0010 February 2015  
www.eaton.com/lighting