

# Steel City®

## Octagon Boxes



54-C-1

54-C-6

54-C-7



54-C-3-1/2

54-C-3

54-C-3-1



54-C-3-1-1/4

54-C-14

5401-LR



5402-LR



SHR 1/2 &amp; 3/4

### 4" Octagon and Round Box Covers

Cat. No.	Raised	Description	Cu. In. Cap.	Std. Ctn.
54-C-1	—	Flat, blank	—	50
54-C-6	—	Flat, with 1/2" KO	—	50
54-C-7	5/8"	With 1/2" KO	3.5	25
54-C-3-1/2	1/2"	Center blanked with tapped ears on 2 3/4" centers	3.0	25
54-C-3	5/8"	Center blanked with tapped ears on 2 3/4" centers	3.5	25
54-C-3-1	1"	Center blanked with tapped ears on 2 3/4" centers	5.8	25
54-C-3-1-1/4	1 1/4"	Center blanked with tapped ears on 2 3/4" centers	7.3	25
54-C-14	5/8"	For single device	3.5	25
5401-LR	—	Flat, center blanked for single receptacle—1 1/2" dia. hole	—	25
5402-LR	—	Flat, center blanked for duplex receptacle	—	25

For Swivel Covers see below and page A26.

### Swivel Hangers

Cat. No.	Bar Lgth. (in.)	Description	Slot (in.)	Std. Ctn.
SHR 1/2 & 3/4	—	Swivel Hanger for 4" Octagonal Boxes	—	25

UL Listed for 50 lb. Fixture Support.