

-	MAW-600H-(gloss)	(1) smart dimmer (1) Claro wallplate	600 W, single pole	1,2,3
-	MAW-603RH-(gloss)	(1) smart dimmer (1) companion dimmer (2) Claro wallplates	600 W	1,2,3

Dual Dimmers

[Return to Top](#)

Boxed	Clamshell	Description	Capacity	Notes
MA-L3L3-	MA-L3L3HW-WH Includes Claro wallplate. (white only)	single pole	300 W each dimmer	no neutral required (1)

Dimmer/Switch

[Return to Top](#)

Boxed	Clamshell	Description	Capacity	Notes
MA-L3S25-	MA-L3S25HW-WH Includes Claro wallplate. (white only)	single pole	Dimmer: 300 W Switch: 2.5 A light or general purpose fan	no neutral required (1)

Magnetic Low Voltage

[Return to Top](#)

Model	Description	Capacity	Notes
Preset Smart Dimmer			
MALV-600-(gloss)	single pole or multi-location	600 VA (450 W)	1, 2
MSCLV-600M-(satin)			
MALV-1000-(gloss)		1,000 VA (800 W)	
MSCLV-1000M-(satin)			
Companion Dimmer			
MA-R- (gloss)	Full function dimming from up to 9 additional locations		1, 2
MSC-AD- (satin)			

Electronic Low Voltage

[Return to Top](#)

[Maestro](#) >> [Products](#) >> [Maestro Dimmers](#)

Maestro Dimmers

- [Incandescent](#)
- [Dual Dimmers](#)
- [Dimmer/Switch](#)
- [Magnetic Low Voltage](#)
- [Electronic Low Voltage](#)
- [Fluorescent](#)
- [Footnotes](#)

Customer Service
 1.888.LUTRON1
 8AM-8PM EST

Technical Assistance
 1.800.523.9466
 24 hours a day,
 7 days a week



Maestro Dimmer and Claro faceplate in White (WH)

[Click Here](#) to learn about the features and benefits of various Maestro dimmer models, including those for various load types and dual applications.

Listed; Lutron controls are rated at 120 V~ , 60 Hz unless otherwise noted.

Available in 7 gloss and 20 satin colors.



Maestro in Black (BL) Claro faceplate in Stainless Steel (SS)

Request:
 Printed Literature
 Sales Contact

Incandescent







[Return to Top](#)

Online Tech Support



Boxed	Clamshell	Description	Capacity	Notes
Preset Smart Dimmer				
MA-600-(gloss)	MA-600H-(gloss)	Single pole or multi-location smart dimmer	600 W	1.2
MSC-600M-(satin)	MSC-600H-(select satin, single pole only)			
MA-1000-(gloss)	-		1,000 W	1.2
MSC-1000M-(satin)	-			
Companion Dimmer				
MA-R-(gloss)	-	Use with MA-600, MSC-600, MA-1000, or MSC-1000	Dimming from up to 9 additional locations	1.2
MSC-AD-(satin)	-			
Smart Dimmer Packages				

available models

source type

-  incandescent lighting
-  magnetic low voltage lighting
-  electronic low voltage lighting
-  fluorescent lighting
-  quiet 7-speed fan controls
-  quiet 7-speed fan/light controls

control locations

-  single pole
-  multi-location

available colors




colors (gloss finish)

- | | |
|------------------------|-----------------|
| WH white | GR gray |
| IV ivory | BR brown |
| AL almond | BL black |
| LA light almond | |

colors (satin finish)

- | | |
|------------------------|---------------------|
| HT hot | SG sea glass |
| MR merlot | SI sienna |
| TC terracotta | MN midnight |
| GB greenbriar | TP taupe |
| BG bluestone | ES eggshell |
| DS desert stone | BI biscuit |
| ST stone | SW snow |
| LS limestone | |

colors & finishes key

-  available in gloss finish
-  available in satin finish
-  available in all gloss and satin finishes

See page 17 for color swatches.

Maestro® | Multi-location Dimmers with Designer Styling.

What Is Maestro	New Maestro Wireless	Products	TechnicalInfo
---------------------------------	--------------------------------------	--------------------------	-------------------------------

Maestro Family

[Maestro >>](#) [What Is Maestro >>](#) [Maestro Family](#)

[Dimmers](#)

[Maestro Wireless](#)

[Maestro IR Dimmers](#)

[Fan Controls](#)

[Maestro IR Fan Controls](#)

[Maestro IR Fan/Light](#)

[Timers](#)

Customer Service
 1.888.LUTRON1
 8AM-8PM EST

Technical Assistance
 1.800.523.9466
 24 hours a day,
 7 days a week

Request:
 Printed Literature
 Sales Contact

Online Tech Support

Maestro offers a full range of designer light controls, fan controls, and timers, in 27 colors. Adjust your lights and fans from anywhere in the room.

- ⌘ High performance personalized light control.
- ⌘ Dimmers offer customizable delayed fade to off, letting you leave the room before lights go out.
- ⌘ LEDs glow softly in the dark for easy dimmer location and show preset light level.
- ⌘ Multi-location dimming compatible with 3-way wiring for easy installation and retrofit.
- ⌘ Companion dimmers provide full range dimming from up to ten locations.
- ⌘ Maestro IR provides infrared remote control of lights and fans.
- ⌘ Fan controls offer 7 quiet speeds for enhanced comfort.
- ⌘ Timer can be set to operate fan or light for 5-60 minutes before turning off automatically.
- ⌘ Power failure memory - Maestro remembers your settings even after a power interruption.
- ⌘ Superior suppression of interference with radio and TV.



Maestro dimmers are available for incandescent, halogen, magentic low voltage, and electronic low voltage applications. Lutron controls are rated at 120VAC, 60Hz unless otherwise noted.

Dimmers

[Return to Top](#)



Maestro Dimmer

Dimmer Features

- ⌘ Full-range dimming possible from up to ten locations.
- ⌘ LEDs show preset light level when lights are off.
- ⌘ Lights fade up and down smoothly allowing your eyes to adjust to changing light levels.
- ⌘ Customizable delayed fade to off lets you leave the room before the lights go out.
- ⌘ Standard 3- and 4-way wiring for easy installation and retrofit.

Designer Series Standard Features

- ⌘ Power failure memory
- ⌘ Superior RFI suppression

[Click here](#) for Maestro dimmer models.

Maestro Wireless

[Return to Top](#)

Safe Entry™ dimmer with wireless controller

Available Now through select electrical suppliers and lighting showrooms.



Maestro Wireless Dimmer and Controller

- ⌘ Never enter a dark home again.™
- ⌘ Control your lighting from outside or inside your home up to 100 feet.
- ⌘ Compatible with Homelink-equipped vehicles.
- ⌘ Reliable radio frequency (RF) technology.
- ⌘ Control up to three dimmers with one wireless controller.
- ⌘ Control each dimmer with up to four wireless controllers.
- ⌘ Recall your favorite light level with the touch of a button.
- ⌘ LEDs glow softly in the dark for easy dimmer location and show preset light level when product is off.
- ⌘ Customizable delayed fade to off ranging from 10-60 seconds lets you leave the room before lights go out.
- ⌘ Full range dimming possible from up to ten locations.
- ⌘ Multi-location dimming compatible with 3-way wiring for easy installation and retrofit.
- ⌘ Power failure memory - dimmer remembers your settings even after a power interruption.
- ⌘ Superior suppression of interference with radio and TV.

[Click here](#) for Maestro Wireless models.

[Launch Wireless Demo](#)

Maestro IR Dimmers

[Return to Top](#)

Adjust your lights from anywhere in the room *



Maestro IR Dimmer

- ⌘ Silver button recalls your favorite light level.
- ⌘ Compatible with most learning remote controls.
- ⌘ LEDs glow softly in the dark for easy dimmer location and show preset light level when product is off.
- ⌘ Customizable delayed fade to off lets you leave the room before lights go out.
- ⌘ Full range dimming possible from up to ten locations.
- ⌘ Multi-location dimming compatible with 3-way wiring for easy installation and retrofit.
- ⌘ Power failure memory - Maestro remembers your settings even after a power interruption.
- ⌘ Superior suppression of interference with radio and TV.

[Click here](#) for Maestro IR dimmer models.

* up to 30 feet; range may vary due to local conditions.