

Steel City®

Thinwall Conduit Fittings (EMT)

Set Screw Couplings – Steel



"A" Cat#	Conduit Size	Inner Pack	Outer Pack	Availability
TK121A	½"	50	500	Available Now!
TK122A	¾"	50	250	Available Now!
TK123A	1"	25	100	Available Now!
TK124A	1¼"	-	25	Available Now!
TK125A	1½"	-	25	Available Now!
TK126A	2"	-	25	Available Now!
TK127A	2½"	-	10	Available Fall 2002!
TK128A	3"	-	5	Available Fall 2002!
TK129A	3½"	-	5	Available Fall 2002!
TK1210A	4"	-	5	Available Fall 2002!

U.L. File No. E-16592



- Concrete Tight, when taped
- Zinc Plated

Thomas & Betts

Thinwall Conduit Fittings (EMT)

Here's How The Steel City Part Number System Works

Easy to identify alphabetical prefixes:

BG – Bushings, Grounding
BI – Bushings, Insulated
BL – Blanks
BU – Bushings
CB – Clamp Back
EK – 3 Piece Coupling
GA – Ground Clamp (armored ground wire)
GC – Ground Clamp
HA – Heavywall Adapter
HC – Heavywall Connector
HK – Heavywall Coupling
HO – Heavywall Offset
HS – Heavywall Strap
LG – Locknut, Grounding
LN – Locknut
LT – Liquidtight
NC – Nonmetallic Sheathed Cable Connector
NS – Nonmetallic Sheathed Cable Strap
SH – Service Entrance Fitting
SL – Service Ells
SR – Sealing Rings
LS – Locknut, Sealing
TC – Thinwall Connectors
TK – Thinwall Couplings
TO – Thinwall Offset
TS – Thinwall Strap
TX – Thinwall to Flexible Metallic Conduit Fitting
UC – Utility Connector
WA – Washer
XC – Armored Cable or Flexible Metallic Conduit Connector
XK – Armored Cable or Flexible Metallic Conduit Coupling

1st Digit – Material

1 = Steel
2 = Die Cast
3 = Combination Steel and Die Cast
4 = Malleable
5 = Plastic
6 = Aluminum
7 = Steel Insulated
8 = Die Cast Insulated
9 = Malleable Insulated

2nd Digit – Method

1 = Compression
2 = Set Screw
3 = Other

3rd/4th Digit Size

1 = ½"
2 = ¾"
3 = 1"
4 = 1¼"
5 = 1½"
6 = 2"
7 = 2½"
8 = 3"
9 = 3½"
10 = 4"
11 = 5"
12 = 6"

A few examples of the three digit identification system for thinwall fittings are:

TK-111	½" steel, compression type coupling
TC-714	1¼" steel insulated compression type connector
TC-822	¾" die cast, insulated, set-screw type connector